


FLLD4120ATHT6

Aliases (LLD4120ATHT6)

KEMET, FLLD4-TH, EMI/RFI Filters, Noise Suppression, 530 VAC, 120 A, 250x140x140mm



Click [here](#) for the 3D model.

Dimensions

L	250mm NOM
W	140mm NOM
H	140mm NOM
L1	200mm NOM
W1	153.5mm NOM
W2	170mm NOM
J	55mm NOM
K	6.5mm NOM
M (Earth)	Threaded Studs M10

Packaging Specifications

Packaging	Bulk
Packaging Quantity	1
Component Weight	5300 g

General Information

Series	FLLD4-TH
Style	Chassis Mount
Description	EMI Filter, Chassis Mount, Compact
Features	High Performance
Phase	Three-phase + Neutral
RoHS	Yes
Qualifications	IEC/EN 60939
Terminal Type	Terminal Block

Specifications

Voltage AC	530 VAC
Rated Frequency	50-60 Hz
Rated Current	120 A (50°C)
Rated Temperature	50°C
Temperature Range	-25/+100°C
Climate Category	25/100/21
Test Voltage DC (P to P)	2250 VDC
Test Voltage DC (P to E)	3000 VDC
Power Loss	30 W (25°C 50 Hz)
Leakage Current	11 mA