



Pushing Performance  
Since 1945

# HPP V4 RJ45 coupler Cat.6A



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 345 1560
Specification	HPP V4 RJ45 coupler Cat.6A
HARTING eCatalogue	<a href="https://b2b.harting.com/09453451560">https://b2b.harting.com/09453451560</a>

## Identification

Category	Connectors
Series	HARTING PushPull (V4)
Identification	RJ45
Element	Coupler

## Version

Shielding	Fully shielded, 360° shielding contact
Number of contacts	8
Locking type	PushPull

## Technical characteristics

Transmission characteristics	Cat. 6A Class E <sub>A</sub> up to 500 MHz
Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
	10 Gbit/s
Limiting temperature	-40 ... +70 °C
Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP65
	IP67

## Material properties

Material (hood/housing)	Thermoplastic
-------------------------	---------------



**Pushing Performance**  
Since 1945

## Material properties

Colour (hood/housing)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Antimony trioxide
	Lead
	Nickel

## Specifications and approvals

Specifications	IEC 61076-3-106 Variant 4 (V4) EN 45545-2
Approvals	DNV GL

## Commercial data

Packaging size	1
Net weight	35 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140059979
ETIM	EC001264
eCl@ss	27440190 Industry connector (unspecified)