



Click [here](#) for the 3D model.

### General Information

|               |                                 |
|---------------|---------------------------------|
| Series        | SSRH7H-M                        |
| Style         | Through-Hole                    |
| RoHS          | Yes                             |
| Notes         | M17 Lot No.                     |
| Miscellaneous | Temperature Rise Maximum: 55 K. |
| Core          | Mn-Zn Ferrite                   |

### Specifications

|                   |                 |
|-------------------|-----------------|
| Voltage AC        | 250 VAC         |
| Inductance        | 2.9 mH (10 kHz) |
| Current           | 1.7 A           |
| Temperature Range | -25/+120°C      |
| DC Resistance     | 120 mOhms       |

### Dimensions

|           |                |
|-----------|----------------|
| L         | 18mm MAX       |
| T         | 14.5mm MAX     |
| H         | 12mm MAX       |
| LL        | 3.5mm +/-0.5mm |
| S         | 13mm NOM       |
| SI        | 10mm NOM       |
| Wire Size | 0.7mm          |

### Packaging Specifications

|                    |      |
|--------------------|------|
| Packaging          | Tray |
| Packaging Quantity | 600  |
| Component Weight   | 5 g  |