

Contact Layout

41



22#22D, 3#20
11#16, 2#12
3#8 Triax

| 25-41 | | | | | |
|-------|--------|--------|-----|-------|-------|
| Ctc | X | Y | Ctc | X | Y |
| A | 0 | 10.79 | Y | -5.37 | 7.92 |
| B | 7.09 | 11.34 | Z | 3.32 | 5.72 |
| C | 10.77 | 7.92 | a | 7.96 | -0.42 |
| D | 12.94 | 3.39 | b | 0 | -6.6 |
| E | 13.27 | -1.62 | c | -7.96 | -0.42 |
| F | 8.17 | -6.44 | d | -3.32 | 5.72 |
| G | 4.67 | -12.53 | e | 0 | 4.48 |
| H | 0 | -13.37 | f | 3.02 | 3.07 |
| J | -4.67 | -12.53 | g | 5.32 | 0.005 |
| K | -8.17 | -6.44 | h | 3.7 | -2.43 |
| L | -13.27 | -1.62 | i | 2.38 | -4.74 |
| M | -12.94 | 3.39 | j | -2.38 | -4.74 |
| N | -10.77 | 7.92 | k | -3.7 | -2.43 |
| P | -7.09 | 11.34 | m | -5.32 | 0.005 |
| R | 5.37 | 7.92 | n | -3.02 | 3.07 |
| S | 7.32 | 3.91 | p | 0 | 1.81 |
| T | 10.39 | 0.67 | q | 2.59 | -0.01 |
| U | 1.77 | -9.66 | r | 0 | -3.53 |
| V | -1.77 | -9.66 | s | -2.59 | -0.01 |
| W | -10.39 | 0.67 | t | 0 | -0.86 |
| X | -7.32 | 3.91 | | | |

Panel cutout

JAM NUT RECEPTACLE (TYPE 7)



| Dim | Nominal |
|-----|---------------|
| B | 43.43+0/-0.25 |
| ØC | 44.7+0.25/-0 |

SOURIAU shall not be liable for any non-conformity or damage due to a use of the Products which does not comply with the Specifications issued by either of the Parties or by a third party (professional recommendation, technical notice.)

| Country | Jurisdiction & Control List |
|---------|-----------------------------|
| FR | Not Listed |

PN: 8D725W41BB

| | | | |
|----------------|------------------------------------|--------------------------------|---|
| A | 05-10-2016 | First Release | |
| ISS | DATE | Latest modification - by | MOD N° |
| Designed By: | | Date: | CUSTOMER DRAWING |
| TITLE | Aluminium Receptacle 8D series | | |
| SCALE | | General linear Tolerances: ±-- | NPRDS / PROJECT 859 |
| NA | | | |
| SOURIAU | WWW.SOURIAU.COM | | This document is the property of SOURIAU it must not be reproduced or communicated without permission |
| FORMAT | SOURIAU DRG N° 8D725W41BB-C | | SHEET 2/2 |