

## Cat6 RJ45 Modular Connector Plug with Load Bar, Solid/Stranded Conductor Round Cat6 Wire, 100-pack

MODEL NUMBER: N230-100



### Highlights

- 100 Pack Cat6 RJ45 Plug with Load Bar
- 50 Micron Gold Contacts
- Staggered design reduces NEXT
- Supports cable jacket OD's between 4.5mm to 6.3mm
- Supports individual twisted pair conductor wire sizes up to 1.1mm.

### Package Includes

100 each RJ45 Cat6 Plugs and Load-Bars

### Description

These Cat6 RJ45 plugs can be used with solid or stranded conductor Cat6 wire. Included load-bars add to ease of termination and virtually foolproof results. Staggered up-down design for enhanced performance and reduction of near-end cross-talk (NEXT). 50 micro-inch gold contacts for durability and longevity. Polycarbonate housing, UL94-V2.

### Features

- Unshielded Cat6 RJ45 plug with Load-Bar for easy termination
- 50 micron Gold plating
- Use with Solid or Stranded conductor 4-pair Cat6 cable
- Staggered nose pattern reduces NEXT
- Works with most available RJ45 crimp tools ( excluding AMP )
- Supports cable jacket OD's between 4.5mm to 6.3mm
- Supports individual twisted pair conductor wire sizes up to 1.1mm.

## Specifications

OVERVIEW	
UPC Code	037332173201
Technology	Cat6
PHYSICAL	
Color	White

# TRIPP-LITE

by **EAT•N**

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States

Connector Color	White
Shipping Dimensions (hwd / in.)	8.70 x 7.10 x 0.50
Shipping Dimensions (hwd / cm)	22.10 x 18.03 x 1.27
Shipping Weight (lbs.)	0.38
Shipping Weight (kg)	0.17
<b>CONNECTIONS</b>	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	Trade Agreements Act (TAA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

# TRIPP-LITE

by **EAT•N**

© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.