

JML06

JML06 技术参数

容量范围(PF): 3~120

额定电压:100V

最大电压:220V

绝缘电阻:10000MΩ

工作环境温度:-25~85℃

NominalCapacitance(PF)	CapRange(PF)		Captolerance	TampCoeff (ppm/℃)	QVA LUE	Remark
	Min	Max				
3	1.8	3	3+100%-0%	NPO±250	>500	Black
5	2.4	5	5+100%-0%			Blue
7	2.8	7	7+100%-0%			Blue
10	3.8	10	10+100%-0%	N450±300		White
20	6.5	20	20+100%-0%	N750±300		Red
30	9	30	30+100%-0%	N1000±500		Green
40	12	40	40+100%-0%	N2200±800	>300	Yellow
50	17	50	50+100%-0%		>200	Brown
60	22	60	60+100%-0%			Brown
70	28	70	70+100%-0%			Brown
120	38	120 ₀	120+50%-0%			Brown

JML06-100PF 参考图纸

