


#### **GENERAL DESCRIPTION**

The DS1672 incorporates a 32-bit counter and power-monitoring functions. The 32-bit counter is designed to count seconds and can be used to derive time-of-day, week, month, month, and year by using a software algorithm. A precision, temperature-compensated reference and comparator circuit monitors the status of  $V_{CC}$ . When an out-of-tolerance condition occurs, an internal power-fail signal is generated that forces the reset to the active state. When  $V_{CC}$  returns to an in-tolerance condition, the reset signal is kept in the active state for a period of time to allow the power supply and processor to stabilize.


## **TYPICAL OPERATING CIRCUIT**



#### **FEATURES**

- 32-Bit Counter
- I<sup>2</sup>C Serial Interface
- Automatic Power-Fail Detect and Switch Circuitry
- Power-Fail Reset Output
- Low-Voltage Oscillator Operation (1.3V min)
- Trickle-Charge Capability
- Underwriters Laboratories (UL) Recognized
- -40°C to +85°C Operating Range

#### **PIN CONFIGURATION**



ORDERING INFO	ORMATION			
PART	TEMP RANGE	VOLTAGE (V)	PIN-PACKAGE	<b>TOP MARK*</b>
DS1672-2+	$-40^{\circ}$ C to $+85^{\circ}$ C	2.0	8 PDIP (300 mils)	DS1672-2
DS1672-3+	$-40^{\circ}$ C to $+85^{\circ}$ C	3.0	8 PDIP (300 mils)	DS1672-3
DS1672-33+	-40°C to +85°C	3.3	8 PDIP (300 mils)	DS1672-33
DS1672S-2+	-40°C to +85°C	2.0	8 SO (150 mils)	D1672-2
DS1672S-3+	$-40^{\circ}$ C to $+85^{\circ}$ C	3.0	8 SO (150 mils)	D1672-3
DS1672S-33+	-40°C to +85°C	3.3	8 SO (150 mils)	D167233
DS1672S-3+T&R	$-40^{\circ}$ C to $+85^{\circ}$ C	3.0	8 SO (150 mils)/Tape and Reel	D1672-3
DS1672S-33+T&R	-40°C to $+85$ °C	3.3	8 SO (150 mils)/Tape and Reel	D167233
DS1672U-2+	-40°C to +85°C	2.0	8 µSOP(3mm)	1672 rr -2
DS1672U-3+	-40°C to +85°C	3.0	8 μSOP(3mm)	1672 rr -3
DS1672U-33+	-40°C to +85°C	3.3	8 µSOP(3mm)	1672 rr -33
DS1672U-33+T&R	-40°C to +85°C	3.3	8 µSOP(3mm)/Tape and Reel	1672 rr -33

+ Denotes a lead-free/RoHS-compliant device. \* A "+" anywhere on the top mark denotes a lead-free device. rr = 2-digit alphanumeric revision code.

## **ABSOLUTE MAXIMUM RATINGS**

Voltage Range on Any Pin Relative to Ground	0.5V to +6.0V
Operating Temperature Range (noncondensing)	40°C to +85°C
Storage Temperature Range	-55°C to +125°C
Soldering Temperature (reflow)	+260°C
Lead Temperature (soldering, 10s)	

This is a stress rating only and functional operation of the device at these or any other conditions beyond those indicated in the operation sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods of time can affect device reliability.

## **RECOMMENDED OPERATING CONDITIONS**

 $(T_A = -40^{\circ}C \text{ to } +85^{\circ}C)$  (Note 1)

PA	PARAMETER		MIN	ТҮР	MAX	UNITS	
Supply	DS1672-2	V <sub>CC</sub>	1.8	2.0	5.5		
Supply Voltage	DS1672-3	V <sub>CC</sub>	2.7	3.0	5.5	V	
voltage	DS1672-33	V <sub>CC</sub>	2.97	3.3	5.5		
Logic 1		V <sub>IH</sub>	0.7 x V <sub>CC</sub>		$V_{CC} + 0.5$	V	
Logic 0		V <sub>IL</sub>	-0.5		+0.3 x V <sub>CC</sub>	V	
Backup Sup	ply Voltage	VBACKUP	1.3	3.0	3.63	V	

Note 1: All voltages referenced to ground.

## DC ELECTRICAL CHARACTERISTICS

 $(V_{CCMIN} < V_{CC} < V_{CCMAX}, T_A = -40^{\circ}C \text{ to } +85^{\circ}C.)$  (Note 1)

PARAMETER	SYMBOL	CONDITIONS	MIN	ТҮР	MAX	UNITS
Active Supply Current	I <sub>CCA</sub>	-2: $V_{CC} = 2.2V$			600	μA
(Note 2)		$-3: V_{CC} = 3.3 V$				
		$-33: V_{CC} = 3.63V$				
Standby Current	I <sub>CCS</sub>	-2: $V_{CC} = 2.2V$			500	μA
(Note 3)		$-3: V_{CC} = 3.3V$				
		$-33: V_{CC} = 3.63V$				
Power-Fail Voltage	$V_{PF}$	-2:	2.70	2.88	2.97	V
		-3:	2.45	2.60	2.70	
		-33:	1.58	1.70	1.80	
V <sub>BACKUP</sub> Leakage Current	I <sub>BACKUPLKG</sub>			25	50	nA
Logic 0 Output (Note 4)	I <sub>OL</sub>	$V_{OL} = 0.4 V$			3	mA
Logic 0 Output (Note 4,	I <sub>OL</sub>	$V_{CC} > 2V; V_{OL} = 0.4V$			3	mA
DS1672-2 Only)		$V_{CC} < 2V; V_{OL} = V_{CC}$				
		* 0.2				

Note 1: All voltages referenced to ground.

Note 2:  $I_{CCA}$  specified with SCL clocking at max frequency (400kHz), trickle charger disabled.

Note 3:  $I_{CCS}$  specified with  $V_{CC} = V_{CCTYP}$  and SDA,  $SCL = V_{CCTYP}$ , trickle charger disabled.

Note 4: SDA and  $\overline{RST}$ .

## **DC ELECTRICAL CHARACTERISTICS**

 $(V_{CC} = 0V, T_A = -40^{\circ}C \text{ to } +85^{\circ}C.)$  (Note 5)

PARAMETER	SYMBOL	MIN	ТҮР	MAX	UNITS
V <sub>BACKUP</sub> Current (Oscillator On)	I <sub>BACKUPOSC</sub>		0.425	1	μΑ
V <sub>BACKUP</sub> Current (Oscillator Off)	IBACKUP			200	nA

Note 5: Using the recommended crystal on X1 and X2.

## **CRYSTAL SPECIFICATIONS**<sup>\*</sup>

PARAMETER	SYMBOL	MIN	ТҮР	MAX	UNITS
Nominal Frequency	fo		32.768		kHz
Series Resistance	ESR			45	kΩ
Load Capacitance	CL		6		pF

\*The crystal, traces, and crystal input pins should be isolated from RF generating signals. Refer to Application Note 58: Crystal Considerations for Dallas Real-Time Clocks for additional specifications

#### **AC ELECTRICAL CHARACTERISTICS**

$(V_{CC} = 0V, T_A = -40)$	)°C to +85°C	.)
----------------------------	--------------	----

PARAMETER	SYMBOL	CONDITIONS	DITIONS MIN TYP		MAX	UNITS	
SCL Clock	C	Fast mode	100		400	1 7 7	
Frequency	$\mathbf{f}_{\mathrm{SCL}}$	Standard mode			100	kHz	
Bus Free Time		Fast mode	1.3				
Between a STOP and START Condition	t <sub>BUF</sub>	Standard mode	4.7			μs	
Hold Time		Fast mode	0.6				
(Repeated) START Condition (Note 6)	t <sub>HD:STA</sub>	Standard mode	4.0			μs	
LOW Period of SCL		Fast mode	1.3				
Clock	$t_{LOW}$	Standard mode	4.7			μs	
HIGH Period of SCL	4	Fast mode	0.6				
Clock	t <sub>HIGH</sub>	Standard mode	4.0			μs	
Setup Time for a	t <sub>SU:STA</sub>	Fast mode	0.6				
Repeated START Condition		Standard mode	4.7			μs	
Data Hold Time	t <sub>HD:DAT</sub>	Fast mode	0	0.9			
(Notes 7, 8)		Standard mode	0			μs	
Data Setup Time	t	Fast mode	100			ns	
(Note 9)	t <sub>su:dat</sub>	Standard mode	ndard mode 250				
Rise Time of Both SDA and SCL	4	Fast mode	$20+0.1C_{B}$		300		
SDA and SCL Signals (Note 10)	t <sub>R</sub>	Standard mode			1000	ns	
Fall Time of Both		Fast mode	$20 + 0.1C_{B}$		300		
SDA and SCL Signals (Note 10)	t <sub>F</sub>	Standard mode			300	ns	
Setup Time for STOP		Fast mode	0.6				
Condition	t <sub>su:sto</sub>	Standard mode	4.0			μs	
Capacitive Load for Each Bus Line (Note 10)	Св				400	pF	
I/O Capacitance	C <sub>I/O</sub>			10		pF	

Note 6: After this period, the first clock pulse is generated.

Note 7: A device must internally provide a hold time of at least 300ns for the SDA signal (referenced to the V<sub>IHMIN</sub> of the SCL signal) in order to bridge the undefined region of the falling edge of SCL.

Note 8: The maximum  $t_{HD:DAT}$  has only to be met if the device does not stretch the LOW period ( $t_{LOW}$ ) of the SCL signal.

Note 9: A fast-mode device can be used in a standard-mode system, but the requirement  $t_{SU:DAT} \ge to 250$ ns must then be met. This will automatically be the case if the device does not stretch the LOW period of the SCL signal. If such a device does stretch the LOW period of the SCL signal, it must output the next data bit to the SDA line  $t_R \max + t_{SU:DAT} = 1000 + 250 = 1250$ ns before the SCL line is released.

Note 10: C<sub>B</sub>-Total capacitance of one bus line in pF.

## POWER-UP/POWER-DOWN CHARACTERISTICS


 $(T_A = -40^{\circ}C \text{ to } +85^{\circ}C)$ 

PARAMETER	SYMBOL	MIN	ТҮР	MAX	UNITS
$V_{CC}$ Detect to $\overline{RST}$ ( $V_{CC}$ Falling)	t <sub>RPD</sub>			10	μs
$V_{CC}$ Detect to $\overline{RST}$ ( $V_{CC}$ Rising) (Note 11)	t <sub>RPU</sub>		250		ms
$V_{CC}$ Fall Time; $V_{\text{PF}(\text{MAX})}$ to $V_{\text{PF}(\text{MIN})}$	t <sub>F</sub>	300			μs
$V_{CC}$ Rise Time; $V_{PF(MIN)}$ to $V_{PF(MAX)}$	t <sub>R</sub>	0			μs


Note 11: If the  $\overline{\text{EOSC}}$  bit in the control register is set to logic 1,  $t_{\text{RPU}}$  is equal to 250ms plus the startup time of the crystal oscillator.

## Warning: Negative undershoots below –0.3V while the part is in battery-backed mode can cause loss of data.

## Figure 1. Timing Diagram




#### Figure 2. Power-Up/Power-Down Timing



## **PIN DESCRIPTION**

PIN	NAME	FUNCTION
1, 2	X1, X2	Connections for Standard 32.768kHz Quartz Crystal. The internal oscillator circuitry is designed for operation with a crystal having a specified load capacitance (CL) of 6pF. For more information about crystal selection and crystal layout considerations, refer to <i>Application Note 58: Crystal Considerations with Dallas Real-Time Clocks</i> . The DS1672 can also be driven by an external 32.768kHz oscillator. In this configuration, the X1 pin is connected to the external oscillator signal and the X2 pin is left unconnected.
3	VBACKUP	Battery Input for Any Standard 3V Lithium Cell or Other Energy Source. Battery voltage must be held between 1.3V and 3.63V for proper operation. Diodes placed in series between the power source and the $V_{BACKUP}$ pin may result in improper operation. If a backup supply is not required, $V_{BACKUP}$ must be grounded. UL recognized to ensure against reverse charging current when used in conjunction with a lithium battery (charger disabled). See "Conditions of Acceptability" at <u>www.maxim-ic.com/qa/info/ul</u> .
4	GND	Ground.
5	SDA	Serial-Data Input/Output. SDA is the input/output pin for the $I^2C$ serial interface. The SDA pin is open drain and requires an external pullup resistor.
6	SCL	I <sup>2</sup> C Serial-Clock Input. SCL is used to synchronize data movement on the serial interface and requires an external pullup resistor.
7	RST	Active-Low Reset Output. It functions as a microprocessor reset signal. This pin is an open-drain output and requires an external pullup resistor.
8	V <sub>CC</sub>	Power pin for Primary Power Supply. When $V_{CC}$ is applied within normal limits, the device is fully accessible and data can be written and read. When $V_{CC}$ is below $V_{PF}$ , reads and writes are inhibited.

## Figure 3. Recommended Layout for Crystal




#### **Detailed Description**

The DS1672 provides a 32-bit counter that increments once-per-second. The counter data is accessible via an I<sup>2</sup>C serial interface. A precision, temperature-compensated, voltage reference and comparator circuit monitors  $V_{CC}$ . When  $V_{CC}$  drops below  $V_{PF}$ ,  $\overline{RST}$  becomes active and the interface is disabled to prevent data corruption. The device switches to the backup supply input, which maintains oscillator and counter operation while  $V_{CC}$  is absent. When  $V_{CC}$  rises above  $V_{PF}$ ,  $\overline{RST}$  remains low for a period of time (t<sub>RPU</sub>) to allow  $V_{CC}$  to stabilize.

The block diagram in Figure 4 shows the main elements of the DS1672. As shown, communications to and from the DS1672 occur serially over a  $I^2C$ , bidirectional bus. The DS1672 operates as a slave device on the  $I^2C$  bus. Access is obtained by implementing a START condition and providing a device identification code followed by a register address. Subsequent registers can be accessed sequentially until a STOP condition is executed.

#### Figure 4. Block Diagram



#### **Oscillator Circuit**

The DS1672 uses an external 32.768kHz crystal. The oscillator circuit does not require any external resistors or capacitors to operate. Table 1 specifies several crystal parameters for the external crystal. Figure 4 shows a functional schematic of the oscillator circuit. If using a crystal with the specified characteristics, the startup time is usually less than one second.

#### Table 1. Crystal Specifications\*

PARAMETER	SYMBOL	MIN	TYP	MAX	UNITS	NOTES
Nominal Frequency	Fo		32.768		kHz	
Series Resistance	ESR			45	kΩ	
Load Capacitance	CL		6		pF	

\* The crystal, traces, and crystal input pins should be isolated from RF generating signals. Refer to Application Note 58:

#### **Clock Accuracy**

The accuracy of the clock is dependent upon the accuracy of the crystal and the accuracy of the match between the capacitive load of the oscillator circuit and the capacitive load for which the crystal was trimmed. Additional error will be added by crystal frequency drift caused by temperature shifts. External circuit noise coupled into the oscillator circuit may result in the clock running fast. Refer to *Application Note 5: "Crystal Considerations with Dallas Real-Time Clocks"* for detailed information.

## Address Map

The counter is accessed by reading or writing the first 4 bytes of the DS1672 (00h–03h). The control register and trickle charger are accessed by reading or writing the appropriate register bytes as illustrated in Table 2. If the master continues to send or request more data after the address pointer has reached 05h, the address pointer will wrap around to location 00h.

ADDRESS	<b>B7</b>	<b>B6</b>	B5	<b>B4</b>	<b>B3</b>	<b>B2</b>	<b>B1</b>	<b>B0</b>	FUNCTION
00h								LSB	Counter Byte 1
01h									Counter Byte 2
02h									Counter Byte 3
03h	MSB								Counter Byte 4
04h	EOSC								Control
05h	TCS	TCS	TCS	TCS	DS	DS	RS	RS	Trickle Charger

#### **Table 2. Registers**

## **Power Control**

The device is fully accessible and data can be written and ready only when  $V_{CC}$  is greater than  $V_{PF}$ . However, when  $V_{CC}$  falls below  $V_{PF}$ , (point at which write protection occurs) the internal clock registers are blocked from any access. If  $V_{PF}$  is less than  $V_{BACKUP}$ , the device power is switched from  $V_{CC}$  to  $V_{BACKUP}$  when  $V_{CC}$  drops below  $V_{PF}$ . If  $V_{PF}$  is greater than  $V_{BACKUP}$ , the device power is switched from  $V_{CC}$  to  $V_{BACKUP}$  when  $V_{CC}$  drops below  $V_{BACKUP}$ . Oscillator and counter operation are maintained from the  $V_{BACKUP}$  source until  $V_{CC}$  is returned to nominal levels (see Table 3).

SUPPLY CONDITION	READ/WRITE ACCESS	RST	POWERED BY			
$V_{CC} < V_{PF}, V_{CC} < V_{BACKUP}$	No	Active	VBACKUP			
$V_{CC} < V_{PF}, V_{CC} > V_{BACKUP}$	No	Active	V <sub>CC</sub>			
$V_{CC} > V_{PF}, V_{CC} < V_{BACKUP}$	Yes	Inactive	V <sub>CC</sub>			
$V_{CC} > V_{PF}, V_{CC} > V_{BACKUP}$	Yes	Inactive	V <sub>CC</sub>			

#### Table 3. Power Control

#### **Oscillator Control**

The  $\overline{\text{EOSC}}$  bit (bit 7 of the control register) controls the oscillator when in back-up mode. This bit when set to logic 0 will start the oscillator. When this bit is set to a logic 1, the oscillator is stopped and the DS1672 is placed into a low-power standby mode (I<sub>BACKUP</sub>) when in back-up mode. When the DS1672 is powered by V<sub>CC</sub>, the oscillator is always on regardless of the status of the  $\overline{\text{EOSC}}$  bit; however, the counter is incremented only when  $\overline{\text{EOSC}}$  is a logic 0.

#### **Microprocessor Monitor**

A temperature-compensated comparator circuit monitors the level of  $V_{CC}$ . When  $V_{CC}$  falls to the powerfail trip point, the  $\overline{RST}$  signal (open drain) is pulled active, and read/write access is inhibited. When  $V_{CC}$  returns to nominal levels, the  $\overline{RST}$  signal is kept in the active state for  $t_{RPU}$  (typically) to allow the power supply and microprocessor to stabilize. Note, however, that if the  $\overline{EOSC}$  bit is set to a logic 1 (to disable the oscillator during write protection), the reset signal will be kept in an active state for  $t_{RPU}$  plus the startup time of the oscillator.

#### **Trickle Charger**

The trickle charger is controlled by the trickle charge register. The simplified schematic of Figure 5 shows the basic components of the trickle charger. The trickle charge select (TCS) bit (bits 4–7) controls the selection of the trickle charger. In order to prevent accidental enabling, only a pattern on 1010 will enable the trickle charger. All other patterns will disable the trickle charger. The DS1672 powers up with the trickle charger disabled. The diode select (DS) bits (bits 2, 3) select whether or not a diode is connected between  $V_{CC}$  and  $V_{BACKUP}$ . If DS is 01, no diode is selected or if DS is 10, a diode is selected. The RS bits (bits 0, 1) select whether a resistor is connected between  $V_{CC}$  and  $V_{BACKUP}$  and what the value of the resistor is. The resistor selected by the resistor select (RS) bits and the diode selected by the diode select (DS) bits are as follows:

TCS	TCS	TCS	TCS	DS	DS	RS	RS	FUNCTION
Х	Х	Х	Х	0	0	Х	Х	Disabled
Х	Х	Х	Х	1	1	Х	Х	Disabled
Х	Х	Х	Х	Х	Х	0	0	Disabled
1	0	1	0	0	1	0	1	No diode, $250\Omega$ resistor
1	0	1	0	1	0	0	1	One diode, $250\Omega$ resistor
1	0	1	0	0	1	1	0	No diode, $2k\Omega$ resistor
1	0	1	0	1	0	1	0	One diode, $2k\Omega$ resistor
1	0	1	0	0	1	1	1	No diode, $4k\Omega$ resistor
1	0	1	0	1	0	1	1	One diode, $4k\Omega$ resistor
0	0	0	0	0	0	0	0	Initial default valuedisabled


# Warning: The resistor value of 250 $\Omega$ must not be selected whenever V<sub>CC</sub> is greater than 3.63V.

Diode and resistor selection is determined by the user according to the maximum current desired for battery or super cap charging. The maximum charging current can be calculated as illustrated in the following example. Assume that a system power supply of 3V is applied to  $V_{CC}$  and a super cap is connected to  $V_{BACKUP}$ . Also assume that the trickle charger has been enabled with a diode and resistor R2 between  $V_{CC}$  and  $V_{BACKUP}$ . The maximum current  $I_{MAX}$  would, therefore, be calculated as follows:

 $I_{MAX}$  = (5.0V - diode drop) / R1  $\approx$  (5.0V - 0.6V) / 2k $\Omega~\approx 2.2mA$ 

As the super cap changes, the voltage drop between  $V_{CC}$  and  $V_{BACKUP}$  will decrease and, therefore, the charge current will decrease.

#### Figure 5. Programmable Trickle Charger



## I<sup>2</sup>C Serial Data Bus

The DS1672 supports a bidirectional  $I^2C$  bus and data transmission protocol. A device that sends data onto the bus is defined as a transmitter and a device receiving data as a receiver. The device that controls the message is called a master. The devices that are controlled by the master are slaves. The bus must be controlled by a master device that generates the serial clock (SCL), controls the bus access, and generates the START and STOP conditions. The DS1672 operates as a slave on the  $I^2C$  bus. Connections to the bus are made via the open-drain I/O lines SDA and SCL. Within the bus specifications, a standard mode (100kHz maximum clock rate) and a fast mode (400kHz maximum clock rate) are defined. The DS1672 operates in both modes.

The following bus protocol has been defined (Figure 6):

- Data transfer may be initiated only when the bus is not busy.
- During data transfer, the data line must remain stable whenever the clock line is HIGH. Changes in the data line while the clock line is high will be interpreted as control signals.

Accordingly, the following bus conditions have been defined:

Bus not busy: Both data and clock lines remain HIGH.

**Start data transfer:** A change in the state of the data line from high to low, while the clock line is high, defines a START condition.

**Stop data transfer:** A change in the state of the data line from low to high, while the clock line is high, defines a STOP condition.

**Data valid:** The state of the data line represents valid data when, after a START condition, the data line is stable for the duration of the high period of the clock signal. The data on the line must be changed during the low period of the clock signal. There is one clock pulse per bit of data.

Each data transfer is initiated with a START condition and terminated with a STOP condition. The number of data bytes transferred between the START and the STOP conditions is not limited, and is determined by the master device. The information is transferred byte-wise and each receiver acknowledges with a ninth bit. Within the  $I^2C$  bus specifications a standard mode (100kHz clock rate) and a fast mode (400kHz clock rate) are defined.

Acknowledge: Each receiving device, when addressed, is obliged to generate an acknowledge after the reception of each byte. The master device must generate an extra clock pulse that is associated with this acknowledge bit.

A device that acknowledges must pull down the SDA line during the acknowledge clock pulse in such a way that the SDA line is stable LOW during the HIGH period of the acknowledge related clock pulse. Of course, setup and hold times must be taken into account. A master must signal an end of data to the slave by not generating an acknowledge bit on the last byte that has been clocked out of the slave. In this case, the slave must leave the data line HIGH to enable the master to generate the STOP condition.

Figures 7 and 8 detail how data transfer is accomplished on the  $I^2C$  bus. Depending upon the state of the  $R/\overline{W}$  bit, two types of data transfer are possible:

- 1) **Data transfer from a master transmitter to a slave receiver.** The first byte transmitted by the master is the slave address. Next follows a number of data bytes. The slave returns an acknowledge bit after each received byte.
- 2) **Data transfer from a slave transmitter to a master receiver.** The first byte (the slave address) is transmitted by the master. The slave then returns an acknowledge bit. Next follows a number of data bytes transmitted by the slave to the master. The master returns an acknowledge bit after all received bytes other than the last byte. At the end of the last received byte, a "not acknowledge" is returned.


The master device generates all of the serial clock pulses and the START and STOP conditions. A transfer is ended with a STOP condition or with a repeated START condition. Since a repeated START condition is also the beginning of the next serial transfer, the bus will not be released.

The DS1672 can operate in the following two modes:

1) Slave receiver mode (DS1672 write mode): Serial data and clock are received through SDA and SCL. After each byte is received, an acknowledge bit is transmitted. START and STOP conditions are recognized as the beginning and end of a serial transfer. Address recognition is performed by hardware after reception of the slave address and direction bit (Figure 7). The slave address byte is the first byte received after the START condition is generated by the master. The slave address byte contains the 7-bit DS1672 address, which is 1101000, followed by the direction bit (R/W), which for a write is a 0. After receiving and decoding the slave address byte the DS1672 outputs an acknowledge on the SDA line. After the DS1672 acknowledges the slave address + write bit, the master transmits a word address to the DS1672. This will set the register pointer on the DS1672, with the DS1672 acknowledging the transfer. The master may then transmit zero or more bytes of data,


with the DS1672 acknowledging each byte received. The register pointer will increment after each byte is transferred. The master will generate a stop condition to terminate the data write.

2) Slave transmitter mode (DS1672 read mode): The first byte is received and handled as in the slave receiver mode. However, in this mode, the direction bit will indicate that the transfer direction is reversed. Serial data is transmitted on SDA by the DS1672 while the serial clock is input on SCL. START and STOP conditions are recognized as the beginning and end of a serial transfer (Figure 8). The slave address byte is the first byte received after the START condition is generated by the master. The slave address byte contains the 7-bit DS1672 address, which is 1101000, followed by the direction bit ( $\mathbb{R}/\mathbb{W}$ ), which for a read is a 1. After receiving and decoding the slave address byte the DS1672 outputs an acknowledge on the SDA line. The DS1672 then begins to transmit data starting with the register address pointed to by the register pointer. If the register pointer is not written to before the initiation of a read mode the first address that is read is the last one stored in the register pointer. The DS1672 must receive a "not acknowledge" to end a read.




## Figure 6. Data Transfer on I<sup>2</sup>C Serial Bus

Figure 7. Data Write: Slave Receiver Mode



## Figure 8. Data Read: Slave Transmitter Mode



## THERMAL INFORMATION

PACKAGE	THETA-JA	THETA-JC
8 PDIP (300 mils)	110°C/W	40°C/W
8 SO (150 mils)	128.4°C/W	36°C/W
8 µSOP (3mm)	206.3°C/W	42°C/W

#### **PACKAGE INFORMATION**

For the latest package outline information and land patterns (footprints), go to <u>www.maxim-ic.com/packages</u>. Note that a "+", "#", or "-" in the package code indicates RoHS status only. Package drawings may show a different suffix character, but the drawing pertains to the package regardless of RoHS status.

PACKAGE TYPE	PACKAGE CODE	OUTLINE NO.	LAND PATTERN NO.
8 PDIP (300 mils)	P8+1	<u>21-0043</u>	
8 SO (150 mils)	S8+5	<u>21-0041</u>	<u>90-0096</u>
8 µSOP (3mm)	U8+1	<u>21-0036</u>	<u>90-0092</u>

## REVISION HISTORY

REVISION DATE	DESCRIPTION	PAGES CHANGED
9/11	Updated the Ordering Information, Absolute Maximum Ratings, Recommended Operating Conditions, DC Electrical Characteristics, AC Electrical Characteristics, Pin Description, Trickle Charger, Thermal Information, and Package Information	2, 3, 5, 7, 10, 15

Maxim cannot assume responsibility for use of any circuitry other than circuitry entirely embodied in a Maxim product. No circuit patent licenses are implied. Maxim reserves the right to change the circuitry and specifications without notice at any time.

15 of 15