


Pin数	尺寸A	尺寸B
1		2.0
2	2.0	4.0
3	4.0	6.0
4	6.0	8.0
5	8.0	10.0
6	10.0	12.0
7	12.0	14.0
8	14.0	16.0
9	16.0	18.0
10	18.0	20.0
11	20.0	22.0
12	22.0	24.0
13	24.0	26.0
14	26.0	28.0
15	28.0	30.0
16	30.0	32.0
17	32.0	34.0
18	34.0	36.0
19	36.0	38.0
20	38.0	40.0
21	40.0	42.0
22	42.0	44.0
23	44.0	46.0
24	46.0	48.0
25	48.0	50.0
26	50.0	52.0
27	52.0	54.0
28	54.0	56.0
29	56.0	58.0
30	58.0	60.0
31	60.0	62.0
32	62.0	64.0
33	64.0	66.0
34	66.0	68.0
35	68.0	70.0
36	70.0	72.0
37	72.0	74.0
38	74.0	76.0
39	76.0	78.0
40	78.0	80.0



Specifications :

- Voltage rating: 250VAC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -40°C to +105°C
- Insulation resistance: $\geq 1000 \text{ M } \Omega \text{ Min}$
- Contact resistance: $\leq 20 \text{ M } \Omega \text{ Max}$
- Material: PA6T 94V-0
- Planting Category: 1U"Gold
- Color: Blank-Natural color

X4622 W V S - 2*XX S I -C40 D6.4

① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- ① Series No.
- ② Category: W-wafer
- ③ Welding Board Angle: V- Stright 90°
- ④ Welding Way: S-SMT
- ⑤ Row No -Pin No : XX- 2*01P-40P
- ⑥ Special No.: S-With Post ;
- ⑦ Plastic height: I=2.0mm
- ⑧ Pin length:C=4.0mm
- ⑨ Pin length:D=6.4mm

X4622WVS-2*XXSI-C40D64	PA6T 94V-0	Brass	1U"Gold	X4622F
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Terminal

For and on behalf of
XKB INDUSTRIAL PRECISION CO., LIMITED
香港星坤工業精密有限公司

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
△ X					ANGULAR
△ X					$\pm 5^\circ$
△ X					$L \leq 4$
					± 0.2
					$4 < L \leq 16$
					± 0.3
					$16 < L \leq 63$
					± 0.4
					$L > 63$
					± 0.5

DSND		DATE		SCALE: N/A	MODEL TYPE: X4622WVS-2*XXSI-C40D64		
DWN		DATE		VIEW: 	PART NO.:		
CHKD		DATE		UNIT: mm	2.0 mm Crimp Style Connectors		
APPD		DATE		SIZE: A4	DWG NO.:		
XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT	SHEET	REVISION
					1.0g	1/1	A0

XKB INDUSTRIAL PRECISION CO., LIMITED