




C-HVG30F4

REV	ECN	DESCRIPTION	DATE	MODIFIED
1		UPDATE THE DRAWING	2018.03.14	Jophy.Li

Amphenol PCDSZ
ORIGINAL
PDF Format
R&D




SECTION B-B



安费诺精密连接器(深圳)有限公司
Amphenol PCD Shenzhen

受 控 文 件

2018年3月15日



- NOTE.
1. MATERIAL: COPPER ALLOY/材质:铜合金
 2. PLATING: 5~8um HARD SLIVER OVER 2 ~ 3um COPPER
/电镀: 铜2~3um,银0.05~0.075um
 3. CURRENT RATING:32A/额定电流:32A
 4. CABLE SCOP:4.0mm^2/压线范围:4.0mm^2
 5. PART NUMBER: HVG30 F 4

DIMENSIONS	TOLERANCES	PROJECTION	Amphenol Pcd Shenzhen		TITLE			
			ENGR	2018.03.14	Ø 3.0 SOCKET CONTACT FOR 4.0 MM^2 CABLE			
ANSI Y14.5M UNITS: MM Pro/E FILE	.X ±0.5 .XX ±0.05 ANGLES ±0.5°		Jophy.Li		SIZE	DWG NO.	REV	
ORIGINAL NOT FOR CUSTOMER DISTRIBUTION	THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD SHENZHEN		CHKD		A3	C-HVG30F4	1	
			APPD		CODE: 58982	SCALE: 2:1	SHEET 1	OF 1