




Connectors > Lighting Connectors > Plug & Socket Lighting Connector Accessories



Lighting Connector Accessory Type: **Contact**

Connector System: **Wire-to-Wire**

Sealable: **No**

Connector & Contact Terminates To: **Wire & Cable**

Operating Voltage: **125 VAC**

Features

Product Type Features

Lighting Connector Accessory Type	Contact
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Electrical Characteristics

Operating Voltage	125 VAC
-------------------	---------

Contact Features

Contact Type	Pin
--------------	-----

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Product Compliance




For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 293387-2 NECTOR S OUTLET HV-4 WHITE	 TE Part # 2836287-1 OCEAN_2.0_Applicator-S-062F	 TE Part # 2836287-2 OCEAN_2.0_Applicator-S-062F	 TE Part # 293648-2 NECTOR S PANEL OUTLET LV-2 WHITE
 TE Part # 7-2836287-1 OCEAN_2.0_Applicator-S-062F	 TE Part # 7-2836287-2 OCEAN_2.0_Applicator-S-062F	 TE Part # 7-2836287-7 OCEAN_2.0_SPARE_PART_KIT-062F	 TE Part # 293648-3 NECTOR S PANEL OUTLET HV-4 BLACK



TE Part # 293648-4
NECTOR S PANEL OUTLET LV-2
BLACK

Also in the Series

NECTOR S

Insertion & Extraction Tools(3)

Lighting Cable Assemblies(1)

Plug & Socket Lighting Connector
Accessories(57)

Plug & Socket Lighting Connectors(54)

Customers Also Bought

TE Part #293387-2
NECTOR S OUTLET HV-4 WHITE

TE Part #160684-4
FF 110 REC 0.5-1.0MM2 TPBR

TE Part #2-1903390-3
GIC 2.5 W PLUG HSG 4P BLUE

TE Part #293388-5
NECTOR S PLUG LV-2 WHITE

TE Part #2213229-2
NECTOR M RING NUT, 5/6/7P, 14-17MM

TE Part #293650-4
NECTOR S T-SPLITTER STANDARD

TE Part #7-2151034-2
OCEAN_2.0_APPLICATOR-S-176O

TE Part #7-2151130-1
OCEAN_2.0_Applicator-S-062F130F

TE Part #3-1579021-8
CSV10 FOR HVL 7.5

TE Part #1954563-1
Plug, 4P Rect. Light-N-Lok



Documents

Product Drawings

MICRO QUADLOK SYSTEM PIN CONTACT

English

CAD Files

Customer View Model

ENG_CVM_CVM_293389-1_B1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_293389-1_B1.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_293389-1_B1.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

NECTOR_S_LINE_CONNECTOR_BROCHURE

English

Product Specifications

Application Specification

English