







					ANGLAR	±5°
Δx					L ≤ 4	±0.2
Δx					4 < L ≤ 16	±0.3
Δx					16 < L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						



Current rating:3A AC/DC
额定电流: 3A AC/DC
Temperature range:-40℃-+125℃
温度范围: -40℃-+125℃

K 137635 H M - 2xXX B - N0
① ② ③ ④ ⑤ ⑥ ⑦

- 1.K: XKBTEK-Car Connector
- 2.XKB Series No
- 3.Category:H-Housing
- 4.Category:M-Male Housing
- 5.Row No.Pin No:2xXX-2x08 Pin
- 6.Material:N0-PA66 UL 94V-0






K137635HM-2xXXB-N0	PA66	Gray	K137635TF-B
PART NO	Material	Color	Suitable XKB Terminal

DSND	SCALE: N/A	MODEL TYPE: 2.2mm Automobile connector
DWN	VIEW:	PART NO.: K137635HM-2xXXB-N0
CHKD	UNIT: mm/in	DWG NO.: X-K137635HM-2xXXB-N0
APPD	SIZE: A4	WEIGHT
		SHEET
		REVISION
		1/1
		A0




					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED



Current rating:3A AC/DC
 额定电流: 3A AC/DC
 Temperature range:-40℃-+125℃
 温度范围: -40℃-+125℃



K 137635 H M - 2xXX B - N0
 ① ② ③ ④ ⑤ ⑥ ⑦

- 1.K: XKBTEK-Car Connector
- 2.XKB Series No
- 3.Category:H-Housing
- 4.Category:M-Male Housing
- 5.Row No.Pin No:2xXX-2x10 Pin
- 6.Material:N0-PA66 UL 94V-0



K137635HM-2xXXB-N0	PA66	Gray	K137635TF-B
PART NO	Material	Color	Suitable XKB Terminal

DSND		SCALE: N/A	MODEL TYPE: 2.2mm Automobile connector		
DWN		VIEW: 	PART NO.: K137635HM-2xXXB-N0		
CHKD		UNIT: mm/in	DWG NO.: X-K137635HM-2xXXB-N0		
APPD		SIZE: A4	WEIGHT	SHEET	REVISION
L PRECISION CO.,LIMITED				1/1	A0



					ANGLAR	±5°
Δ X					L≤ 4	±0.2
Δ X					4<L≤ 16	±0.3
Δ X					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED





Current rating:3A AC/DC
 额定电流: 3A AC/DC
 Temperature range:-40℃-+125℃
 温度范围: -40℃-+125℃



K 137635 H M - 2xXX B - N0
 ① ② ③ ④ ⑤ ⑥ ⑦

1.K: XKBTEK-Car Connector
 2.XKB Series No
 3.Category:H-Housing
 4.Category:M-Male Housing
 5.Row No.Pin No:2xXX-2x14 Pin
 6.Material:N0-PA66 UL 94V-0



K137635HM-2xXXB-N0	PA66	Gray	K137635TF-B
PART NO	Material	Color	Suitable XKB Terminal

DSND		SCALE: N/A	MODEL TYPE: 2.2mm Automobile connector		
DWN		VIEW: 	PART NO.: K137635HM-2xXXB-N0		
CHKD		UNIT: mm/in	DWG NO.: X-K137635HM-2xXXB-N0		
APPD		SIZE: A4	WEIGHT	SHEET	REVISION
L PRECISION CO.,LIMITED				1/1	A0

XKB



XKB INDUSTRIAL PRECISION CO.,LIMITED

ANGLAR	±5°
L≤ 4	±0.2
4<L≤ 16	±0.3
16<L≤ 63	±0.4
L> 63	±0.5

UNSPECIFIED TOLERANCES


www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

ΔX	DESCRIPTION	DATE	REVISED	APPROVED
ΔX				
ΔX				
MARK				
REVISIONS				



K 137635 H M - 2xXX B - N0
 (1) (2) (3) (4) (5) (6) (7)

38.3 [1.520]±0.3







DSND		SCALE: N/A	MODEL TYPE: 2.2mm Automobile connector		
DWN		VIEW: 	PART NO.: K137635HM-2xXXB-N0		
CHKD		UNIT: mm/in	DWG NO.: X-K137635HM-2xXXB-N0		
APPD		SIZE: A4			
PRECISION CO., LIMITED			WEIGHT	SHEET 1/1	REVISION A0

					ANGLAR	±5°
Δx					L ≤ 4	±0.2
Δx					4 < L ≤ 16	±0.3
Δx					16 < L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKLE

XKB INDUSTRIAL PRECISION CO.,LIMITED



Current rating:3A AC/DC
额定电流: 3A AC/DC
Temperature range:-40℃-+125℃
温度范围: -40℃-+125℃

K 137635 H M - 2xXX B - N0
① ② ③ ④ ⑤ ⑥ ⑦





- 1.K: XKBTEK-Car Connector
- 2.XKB Series No
- 3.Category:H-Housing
- 4.Category:M-Male Housing
- 5.Row No.Pin No:2xXX-2x18 Pin
- 6.Material:N0-PA66 UL 94V-0

K137635HM-2xXXB-N0	PA66	Gray	K137635TF-B
PART NO	Material	Color	Suitable XKB Terminal

					ANGLAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						



DSND		SCALE: N/A	MODEL TYPE: 2.2mm Automobile connector
DWN		VIEW:	PART NO.: K137635HM-2xXXB-N0
CHKD		UNIT: mm/in	DWG NO.: X-K137635HM-2xXXB-N0
APPD		SIZE: A4	WEIGHT SHEET REVISION
XKB INDUSTRIAL PRECISION CO.,LIMITED			1/1 A0



Current rating:3A AC/DC
额定电流: 3A AC/DC
Temperature range:-40℃~+125℃
温度范围: -40℃~+125℃

K 137635 H M - 2xXX B - N0
① ② ③ ④ ⑤ ⑥ ⑦

- 1.K: XKBTEK-Car Connector
- 2.XKB Series No
- 3.Category:H-Housing
- 4.Category:M-Male Housing
- 5.Row No.Pin No:2xXX-2x20 Pin
- 6.Material:N0-PA66 UL 94V-0

K137635HM-2xXXB-N0	PA66	Gray	K137635TF-B
PART NO	Material	Color	Suitable XKB Terminal

DSND		SCALE: N/A	MODEL TYPE: 2.2mm Automobile connector
DWN		VIEW:	PART NO.: K137635HM-2xXXB-N0
CHKD		UNIT: mm/in	DWG NO.: X-K137635HM-2xXXB-N0
APPD		SIZE: A4	

					ANGLAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0