





Current rating:3A AC/DC  
额定电流: 3A AC/DC  
Temperature range:-40℃~+125℃  
温度范围: -40℃~+125℃

K 137635 H M - 2xXX B - N0  
① ② ③ ④ ⑤ ⑥ ⑦

- 1.K: XKBTEK-Car Connector
- 2.XKB Series No
- 3.Category:H-Housing
- 4.Category:M-Male Housing
- 5.Row No.Pin No:2xXX-2x06 Pin
- 6.Material:N0-PA66 UL 94V-0




|                    |          |       |                       |
|--------------------|----------|-------|-----------------------|
| K137635HM-2xXXB-N0 | PA66     | Gray  | K137635TF-B           |
| PART NO            | Material | Color | Suitable XKB Terminal |

|                         |                                                                                             |                                           |       |          |
|-------------------------|---------------------------------------------------------------------------------------------|-------------------------------------------|-------|----------|
| DSND                    | SCALE: N/A                                                                                  | MODEL TYPE:<br>2.2mm Automobile connector |       |          |
| DWN                     | VIEW:  | PART NO.:<br>K137635HM-2xXXB-N0           |       |          |
| CHKD                    | UNIT: mm/in                                                                                 | DWG NO.:<br>X-K137635HM-2xXXB-N0          |       |          |
| APPD                    | SIZE: A4                                                                                    | WEIGHT                                    | SHEET | REVISION |
| L PRECISION CO.,LIMITED |                                                                                             |                                           | 1/1   | A0       |

|                                                   |             |      |         |          |                        |      |
|---------------------------------------------------|-------------|------|---------|----------|------------------------|------|
|                                                   |             |      |         |          | ANGLAR                 | ±5°  |
| Δx                                                |             |      |         |          | L≤ 4                   | ±0.2 |
| Δx                                                |             |      |         |          | 4<L≤ 16                | ±0.3 |
| Δx                                                |             |      |         |          | 16<L≤ 63               | ±0.4 |
| MARK                                              | DESCRIPTION | DATE | REVISED | APPROVED | L> 63                  | ±0.5 |
| REVISIONS                                         |             |      |         |          | UNSPECIFIED TOLERANCES |      |
| www.helloxkb.com   www.helloxkb.cn   www.xk-dg.cn |             |      |         |          |                        |      |

XKB




XKB INDUSTRIAL PRECISION CO.,LIMITED



Current rating:3A AC/DC  
额定电流: 3A AC/DC  
Temperature range:-40℃-+125℃  
温度范围: -40℃-+125℃

K 137635 H M - 2xXX B - N0  
① ② ③ ④ ⑤ ⑥ ⑦

- 1.K: XKBTEK-Car Connector
- 2.XKB Series No
- 3.Category:H-Housing
- 4.Category:M-Male Housing
- 5.Row No.Pin No:2xXX-2x08 Pin
- 6.Material:N0-PA66 UL 94V-0






|                    |          |       |                       |
|--------------------|----------|-------|-----------------------|
| K137635HM-2xXXB-N0 | PA66     | Gray  | K137635TF-B           |
| PART NO            | Material | Color | Suitable XKB Terminal |

|                         |  |                                                                                             |                                           |       |          |
|-------------------------|--|---------------------------------------------------------------------------------------------|-------------------------------------------|-------|----------|
| DSND                    |  | SCALE: N/A                                                                                  | MODEL TYPE:<br>2.2mm Automobile connector |       |          |
| DWN                     |  | VIEW:  | PART NO.:<br>K137635HM-2xXXB-N0           |       |          |
| CHKD                    |  | UNIT: mm/in                                                                                 | DWG NO.:<br>X-K137635HM-2xXXB-N0          |       |          |
| APPD                    |  | SIZE: A4                                                                                    |                                           |       |          |
| L PRECISION CO.,LIMITED |  |                                                                                             | WEIGHT                                    | SHEET | REVISION |
|                         |  |                                                                                             |                                           | 1/1   | A0       |




|                                                   |             |      |         |          |                        |      |
|---------------------------------------------------|-------------|------|---------|----------|------------------------|------|
|                                                   |             |      |         |          | ANGLAR                 | ±5°  |
| Δx                                                |             |      |         |          | L≤ 4                   | ±0.2 |
| Δx                                                |             |      |         |          | 4<L≤ 16                | ±0.3 |
| Δx                                                |             |      |         |          | 16<L≤ 63               | ±0.4 |
| MARK                                              | DESCRIPTION | DATE | REVISED | APPROVED | L> 63                  | ±0.5 |
| REVISIONS                                         |             |      |         |          | UNSPECIFIED TOLERANCES |      |
| www.helloxkb.com   www.helloxkb.cn   www.xk-dg.cn |             |      |         |          |                        |      |

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED



Current rating:3A AC/DC  
额定电流: 3A AC/DC  
Temperature range:-40℃-+125℃  
温度范围: -40℃-+125℃



K 137635 H M - 2xXX B - N0  
① ② ③ ④ ⑤ ⑥ ⑦

- 1.K: XKBTEK-Car Connector
- 2.XKB Series No
- 3.Category:H-Housing
- 4.Category:M-Male Housing
- 5.Row No.Pin No:2xXX-2x10 Pin
- 6.Material:N0-PA66 UL 94V-0

|                    |          |       |                       |
|--------------------|----------|-------|-----------------------|
| K137635HM-2xXXB-N0 | PA66     | Gray  | K137635TF-B           |
| PART NO            | Material | Color | Suitable XKB Terminal |



|                         |  |                                                                                             |                                           |       |          |
|-------------------------|--|---------------------------------------------------------------------------------------------|-------------------------------------------|-------|----------|
| DSND                    |  | SCALE: N/A                                                                                  | MODEL TYPE:<br>2.2mm Automobile connector |       |          |
| DWN                     |  | VIEW:  | PART NO.:<br>K137635HM-2xXXB-N0           |       |          |
| CHKD                    |  | UNIT: mm/in                                                                                 | DWG NO.:<br>X-K137635HM-2xXXB-N0          |       |          |
| APPD                    |  | SIZE: A4                                                                                    | WEIGHT                                    | SHEET | REVISION |
| L PRECISION CO.,LIMITED |  |                                                                                             |                                           | 1/1   | A0       |

|                                                   |             |      |         |          |                        |      |
|---------------------------------------------------|-------------|------|---------|----------|------------------------|------|
|                                                   |             |      |         |          | ANGLAR                 | ±5°  |
| Δ X                                               |             |      |         |          | L≤ 4                   | ±0.2 |
| Δ X                                               |             |      |         |          | 4<L≤ 16                | ±0.3 |
| Δ X                                               |             |      |         |          | 16<L≤ 63               | ±0.4 |
| MARK                                              | DESCRIPTION | DATE | REVISED | APPROVED | L> 63                  | ±0.5 |
| REVISIONS                                         |             |      |         |          | UNSPECIFIED TOLERANCES |      |
| www.helloxkb.com   www.helloxkb.cn   www.xk-dg.cn |             |      |         |          |                        |      |



XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED







Current rating:3A AC/DC  
 额定电流: 3A AC/DC  
 Temperature range:-40℃-+125℃  
 温度范围: -40℃-+125℃



K 137635 H M - 2xXX B - N0  
 ① ② ③ ④ ⑤ ⑥ ⑦

- 1.K: XKBTEK-Car Connector
- 2.XKB Series No
- 3.Category:H-Housing
- 4.Category:M-Male Housing
- 5.Row No.Pin No:2xXX-2x14 Pin
- 6.Material:N0-PA66 UL 94V-0



|                    |          |       |                       |
|--------------------|----------|-------|-----------------------|
| K137635HM-2xXXB-N0 | PA66     | Gray  | K137635TF-B           |
| PART NO            | Material | Color | Suitable XKB Terminal |

|                         |  |                                                                                             |                                           |       |          |
|-------------------------|--|---------------------------------------------------------------------------------------------|-------------------------------------------|-------|----------|
| DSND                    |  | SCALE: N/A                                                                                  | MODEL TYPE:<br>2.2mm Automobile connector |       |          |
| DWN                     |  | VIEW:  | PART NO.:<br>K137635HM-2xXXB-N0           |       |          |
| CHKD                    |  | UNIT: mm/in                                                                                 | DWG NO.:<br>X-K137635HM-2xXXB-N0          |       |          |
| APPD                    |  | SIZE: A4                                                                                    |                                           |       |          |
| L PRECISION CO.,LIMITED |  |                                                                                             | WEIGHT                                    | SHEET | REVISION |
|                         |  |                                                                                             |                                           | 1/1   | A0       |

**XKB**

XKB INDUSTRIAL PRECISION CO.,LIMITED



|          |      |
|----------|------|
| ANGLAR   | ±5°  |
| L≤ 4     | ±0.2 |
| 4<L≤ 16  | ±0.3 |
| 16<L≤ 63 | ±0.4 |
| L> 63    | ±0.5 |

UNSPECIFIED TOLERANCES

| REVISIONS |
|-----------|
|-----------|



www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

| MARK | DESCRIPTION | DATE | REVISED | APPROVED |
|------|-------------|------|---------|----------|
| Δx   |             |      |         |          |
| Δx   |             |      |         |          |
| Δx   |             |      |         |          |

[illegible]

K 137635 H M - 2xXX B - N0  
 (1) (2) (3) (4) (5) (6) (7)

- 1.K: XKBTEK-Car Connector
- 2.XKB Series No
- 3.Category:H-Housing
- 4.Category:M-Male Housing
- 5.Row No.Pin No:2xXX-2x16 Pin
- 6.Material:N0-PA66 UL 94V-0







|                         |  |                                                                                             |                                           |              |                |
|-------------------------|--|---------------------------------------------------------------------------------------------|-------------------------------------------|--------------|----------------|
| DSND                    |  | SCALE: N/A                                                                                  | MODEL TYPE:<br>2.2mm Automobile connector |              |                |
| DWN                     |  | VIEW:  | PART NO.:<br>K137635HM-2xXXB-N0           |              |                |
| CHKD                    |  | UNIT: mm/in                                                                                 | DWG NO.:<br>X-K137635HM-2xXXB-N0          |              |                |
| APPD                    |  | SIZE: A4                                                                                    |                                           |              |                |
| L PRECISION CO.,LIMITED |  |                                                                                             | WEIGHT                                    | SHEET<br>1/1 | REVISION<br>A0 |

|                                             |             |      |         |          |                        |      |
|---------------------------------------------|-------------|------|---------|----------|------------------------|------|
|                                             |             |      |         |          | ANGLAR                 | ±5°  |
| Δx                                          |             |      |         |          | L ≤ 4                  | ±0.2 |
| Δx                                          |             |      |         |          | 4 < L ≤ 16             | ±0.3 |
| Δx                                          |             |      |         |          | 16 < L ≤ 63            | ±0.4 |
| MARK                                        | DESCRIPTION | DATE | REVISED | APPROVED | L > 63                 | ±0.5 |
| REVISIONS                                   |             |      |         |          | UNSPECIFIED TOLERANCES |      |
| www.helloxb.com www.helloxb.cn www.xk-dg.cn |             |      |         |          |                        |      |

XKLE

XKB INDUSTRIAL PRECISION CO.,LIMITED



Current rating:3A AC/DC  
额定电流: 3A AC/DC  
Temperature range:-40℃-+125℃  
温度范围: -40℃-+125℃

K 137635 H M - 2xXX B - N0  
① ② ③ ④ ⑤ ⑥ ⑦





- 1.K: XKBTEK-Car Connector
- 2.XKB Series No
- 3.Category:H-Housing
- 4.Category:M-Male Housing
- 5.Row No.Pin No:2xXX-2x18 Pin
- 6.Material:N0-PA66 UL 94V-0

|                    |          |       |                       |
|--------------------|----------|-------|-----------------------|
| K137635HM-2xXXB-N0 | PA66     | Gray  | K137635TF-B           |
| PART NO            | Material | Color | Suitable XKB Terminal |

|                                                   |             |      |         |          |                        |      |
|---------------------------------------------------|-------------|------|---------|----------|------------------------|------|
|                                                   |             |      |         |          | ANGLAR                 | ±5°  |
| ΔX                                                |             |      |         |          | L≤ 4                   | ±0.2 |
| ΔX                                                |             |      |         |          | 4<L≤ 16                | ±0.3 |
| ΔX                                                |             |      |         |          | 16<L≤ 63               | ±0.4 |
| MARK                                              | DESCRIPTION | DATE | REVISED | APPROVED | L> 63                  | ±0.5 |
| REVISIONS                                         |             |      |         |          | UNSPECIFIED TOLERANCES |      |
| www.helloxkb.com   www.helloxkb.cn   www.xk-dg.cn |             |      |         |          |                        |      |



|                                      |  |             |                                           |
|--------------------------------------|--|-------------|-------------------------------------------|
| DSND                                 |  | SCALE: N/A  | MODEL TYPE:<br>2.2mm Automobile connector |
| DWN                                  |  | VIEW:       | PART NO.:<br>K137635HM-2xXXB-N0           |
| CHKD                                 |  | UNIT: mm/in | DWG NO.:<br>X-K137635HM-2xXXB-N0          |
| APPD                                 |  | SIZE: A4    | WEIGHT SHEET REVISION                     |
| XKB INDUSTRIAL PRECISION CO.,LIMITED |  |             | 1/1 A0                                    |



Current rating:3A AC/DC  
额定电流: 3A AC/DC  
Temperature range:-40℃~+125℃  
温度范围: -40℃~+125℃

K 137635 H M - 2xXX B - N0  
① ② ③ ④ ⑤ ⑥ ⑦

- 1.K: XKBTEK-Car Connector
- 2.XKB Series No
- 3.Category:H-Housing
- 4.Category:M-Male Housing
- 5.Row No.Pin No:2xXX-2x20 Pin
- 6.Material:N0-PA66 UL 94V-0

|                    |          |       |                       |
|--------------------|----------|-------|-----------------------|
| K137635HM-2xXXB-N0 | PA66     | Gray  | K137635TF-B           |
| PART NO            | Material | Color | Suitable XKB Terminal |

|      |  |             |                                           |
|------|--|-------------|-------------------------------------------|
| DSND |  | SCALE: N/A  | MODEL TYPE:<br>2.2mm Automobile connector |
| DWN  |  | VIEW:       | PART NO.:<br>K137635HM-2xXXB-N0           |
| CHKD |  | UNIT: mm/in | DWG NO.:<br>X-K137635HM-2xXXB-N0          |
| APPD |  | SIZE: A4    |                                           |

|                                               |             |      |         |          |                        |      |
|-----------------------------------------------|-------------|------|---------|----------|------------------------|------|
|                                               |             |      |         |          | ANGLAR                 | ±5°  |
| ΔX                                            |             |      |         |          | L≤ 4                   | ±0.2 |
| ΔX                                            |             |      |         |          | 4<L≤ 16                | ±0.3 |
| ΔX                                            |             |      |         |          | 16<L≤ 63               | ±0.4 |
| MARK                                          | DESCRIPTION | DATE | REVISED | APPROVED | L> 63                  | ±0.5 |
| REVISIONS                                     |             |      |         |          | UNSPECIFIED TOLERANCES |      |
| www.helloxkb.com www.helloxkb.cn www.xk-dg.cn |             |      |         |          |                        |      |

**XKLB**

XKB INDUSTRIAL PRECISION CO.,LIMITED

|        |       |          |
|--------|-------|----------|
| WEIGHT | SHEET | REVISION |
|        | 1/1   | A0       |