






标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

PIN

尺寸 (mm)

	尺寸 (mm)		
	A	B	C
02	1.25	4.25	3.05
03	2.50	5.50	4.30
04	3.75	6.75	5.55
05	5.00	8.00	6.80
06	6.25	9.25	8.05
07	7.50	10.50	9.30
08	8.75	11.75	10.55
09	10.00	13.00	11.80
10	11.25	14.25	13.05
11	12.50	15.50	14.30
12	13.75	16.75	15.55
13	15.00	18.00	16.80
14	16.25	19.25	18.05
15	17.50	20.50	19.30
16	18.75	21.75	20.55

PCB Layout
TOL: ±0.05

技术要求:

额定电流: 1.0A AC,DC

(注: AWG32# 0.8A)

额定电压: 125V AC

温度范围: -30° C~85° C

接触电阻: ≤0.02 Ω

绝缘电阻: ≥500M Ω

耐 压: 250V/min

适用导线规格: AWG26#~32#

适用印制板厚度: 0.8mm~1.6mm

2	接触	铜	镀锡	
1	基座	PA66	米色	
序号	品 名	材 质	电镀/颜色	备 注




深圳市虹成电子有限公司

品 名 TITLE	针座
料 号 PART NO	HC-MX1.25-2A

GENERAL TOLERANCES
(UNLESS SPECIFIED)比 例
SCALE

1:1



X.±0.30

X.±5'

单 位
UNIT

MM

制 图
DRAW

AhYe

.X±0.25

.X±3'

张 数
PART NO

1 OF 1

审 核
CHECKED

夏操云

.XX±0.20

.XX±1'

版 本
REV

A

批 准
APPROVE

赵亮亮

