

ST223/产 品 基 本 参 数

安倍:32A 电压:250V 线径:0.08-4mm²

胶壳: 尼龙66工程塑料, UL 94V-0阻燃等级







温度: 110° C (UL), -40° C to T110° C(IEC)

触点材料：紫铜，镀镍

弹片： 不锈钢(301)

推荐剥线长度：9-10mm

接线位数：3位 3进3出



_____		new			2015/5/3		A		瀚源	
ECN BO.		DESCRIPTION.			DATE.		REV.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER				SCALT: 1/2		SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	ST-223-C		UNLESS OTHERWISE SPECIFIED,TOLERANCE:		X.		±0.25
			MODEL NAME	ST-223-C				X.x		±0.20
			3RD ANGLE PROJ	HanElectricity Co.,LTD					ANGULAIR	
				FILE.NO.						