

ST222/产 品 基 本 参 数

安倍:32A 电压:250V 线径:0.08-4mm2

胶壳: 尼龙66工程塑料, UL 94V-0阻燃等级







温度: 110° C (UL),-40° C to T110° C(IEC)

触点材料: 紫铜, 镀镍

弹片: 不锈钢(301)

推荐剥线长度: 9-10mm

接线位数: 2位 2进2出



		new			2015/5/3		A	瀚源	
ECN BO.		DESCRIPTION.			DATE.		REV.		
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER				SCALT: 1/2	SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	ST-222-C		UNLESS OTHERWISE SPECIFIED,TOLERANCE:	X. ±0.25		
			MODEL NAME	ST-222-C			X.x ±0.20		
					X.xx ±0.15				
			3RD ANGLE PROJ	HanElectricity Co.,LTD				ANGULAIR ±3	
								FILE.NO.	