






USB TYPE-C PIN ASSIGNMENTS

PIN NUMBER	SIGNAL NAME	PIN NUMBER	SIGNAL NAME
A1	GND	B12	GND
A2	SSTXp1	B11	SSRXp1
A3	SSTXn1	B10	SSRXn1
A4	VBus	B9	VBus
A5	CC1	B8	SBU2
A6	Dp1	B7	Dn2
A7	Dn1	B6	Dp2
A8	SBU1	B5	CC2
A9	VBus	B4	VBus
A10	SSRXn2	B3	SSTXn2
A11	SSRXp2	B2	SSTXp2
A12	GND	B1	GND




SCALE 1.5:1
RECOMMENDED PCB LAYOUT(TOP VIEW)
THICKNESS 0.8 MM;DEFAULT TOLERANCE:±0.05



制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX-TYPE-C-MWT24P	版本 REV.	A
			X.±0.30	X.*±10°					品名 TITLE	USB CF TYPE DIP+SMT CONN	页次 SHEET	1/1
			.X±0.20	.X*±8°					客户料号 CUTM.NO.			
			.XX±0.10	.XX*±5°					批准 APPROVAL	JADE		
					单位 UNITS	MM	比例 SCALE	1:1	Bossie (博锡)			



SEE DETAIL X



REEL VIEW



	REEL/TRAY	CARTON
CONNECTOR (PCS)	1000	10000

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE	制图 DRAWING	EMMA	料号 PART NO.	BX-TYPE-C-MWT24P	审核 CHECK	EVA	版本 REV.	A
			X.±0.30	X.±10°		品名 TITLE	USB CF TYPE DIP+SMT CONN	批准 APPROVAL	JADE	页次 SHEET	1/1
			.X±0.20	.X°±8°		客户料号 CUTM.NO.					
			.XX±0.10	.XX°±5°							
					单位 UNITS	MM	比例 SCALE	1:1			

Bossie (博锡)