









Rev.	ECN Number	Description	Date	Drawn	Checkd	Approved
A	ECN200718	FIRST RELEASE	04/14'20	PENG	Marlin	Marlin



RECOMMENDED P.C.B. LAYOUT
TOP VIEW(TOLERANCE:±0.05)



RECOMMENDED MASK, THICKNESS:0.1/0.12mm



Notes:

- Material
- (1) Housing:LCP(GF=30%) BLACK UL94 V-0
- (2)Contact:phosphor bronze
point of contact area
Au 0.075um MIN ,over Ni 1.27um MIN,
Solder area
Au 0.03um MIN, over Ni 1.27um MIN,
- (3)Ground contact :phosphor bronze
point of contact area
Au 0.05um MIN ,over Ni 1.27um MIN,
Solder area
Au 0.03um MIN, over Ni 1.27um MIN,
- 2.Coplanarity:0.08mm MAX
- 3.Packing:emboss tape
- 4.Mating partner Part NO.
818002132
- 5.This is "Pb-free" connector
- 6.ROHS compliant
- 7.Production site:Jinxiu Industrial Park.Xitian
Guangdong town,Baoan District,Shenzhen

818016509	Ⓒ	CONTACT	1	COPPER ALLOY/GOLD PLATED OVER Ni
	Ⓓ	HOUSING	1	HIGH TEMP. PLASTIC UL94V-0/BLACK
	Ⓐ	SHELL	1	COPPER ALLOY/Au PLATED OVER Ni
	ITEM	PART NAME	Q'TY	MATERIAL/FINISH
PROD. NO.	BOM LIST			



ELECTRIC
CONNECTOR
TECHNOLOGY

GENERAL TOLERANCE	
XX. ±0.40	
X. ±0.35	X° ±2.0°
.X ±0.25	.X° ±1.0°
.XX ±0.15	.XX° ±0.5°

SCALE:	20:1
UNIT:	mm
SIZE:	A4

DRAWN	PENG
CHECK	
APPROVE	

DATE	04/14'20
DATE	
DATE	

DWG. NO.	600-16509-01
PARTS NO.(INTENDED USE)	818016509

TITLE	CUSTOMER DRAWING USS RF REC CONN,V代,H0.56 USS RF SERIES
REV.	A
SHEET	1/1