




Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)

TOLERANCE TABLE

	TOLERANCE
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:

DATE:

CHECKED:

DATE:

DRAWN:

DATE:

LYF

2024-01-13

TITLE:

深圳市灿科盟实业有限公司
CKMTW CHANKLEMENT INDUSTRY CO., LTD

DWS-2W2M 公头 直插 全金 铆鱼叉锁螺丝

PART. NO. D-DWS02WPM-F000

UNIT	mm	SCALE	free
FILE NO.	CKmtw-DWS-00001	REV.	A

说明:

1. 特性:

额定电压 : 500V AC MAX
额定电流 : 10A, 20A, 30A, 40A
接触电阻 : 30mΩ MAX.
绝缘电阻 : 3000MΩ MIN. at 500V DC
耐电压值 : 1000V AC RMS for 1Minute
温度范围 : -55℃~+105℃
盐雾时间 : 48H

2. 材料:

胶芯 : PBT, rated UL94V-0
接触点 : 铜合金, 镀金1u"-30u"
铁壳 : SPCC, 前壳镀镍后壳镀锡
铜柱 : 铜合金, 镀镍
螺丝 : 铁合金, 镀镍

额定电流	ΦA	PCB孔ΦB
10A	Ø1.80	Ø2.00
20A	Ø2.80	Ø3.00
30A	Ø3.30	Ø3.50
40A	Ø3.80	Ø4.00