





说明:

1. 特性:

额定电压 : 500V AC MAX

小针额定电流 : 5A

大针额定电流 : 10A, 20A, 30A, 40A

接触阻抗 : 30mΩ MAX.

绝缘阻抗 : 3000MΩ MIN. at 500V DC

耐电压值 : 1000V AC RMS for 1Minute

温度范围 : -55℃~+105℃

盐雾时间 : 48H

2. 材料:



胶芯 : PBT, rated UL94V-0

接触点: 铜合金, 镀金1u"-30u"


铁壳 : SPCC, 前壳镀镍后壳镀锡

铜柱 : 铜合金, 镀镍

螺丝 : 铁合金, 镀镍



额定电流	ØA	PCB孔ØB
10A	Ø1.80	Ø2.00
20A	Ø2.80	Ø3.00
30A	Ø3.30	Ø3.50
40A	Ø3.80	Ø4.00



Recommended P.C.B Layout (Top Side)
(PCB BOARD TOLERANCE ±0.05)

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRY CO., LTD			
CHECKED:	DATE:	TITLE: DWS-21W4F 母头 直插 全金 铆鱼叉锁螺丝			
DRAWN: LYF	DATE: 2024-01-13	PART. NO.	D-DWS21WPF-F000		
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-DWS-00030	REV.	A QT00