








UNC 4#40\*2



Recommended P.C.B Layout(Top Side)  
(PCB BOARD TOLERANCE±0.05)



说明:

1. 特性:

额定电压 :500V AC MAX

小针额定电流 :5A

大针额定电流 :10A, 20A, 30A, 40A

接触阻抗 :30mΩ MAX.

绝缘阻抗 :3000MΩ MIN. at 500V DC

耐电压值 :1000V AC RMS for 1Minute

温度范围 : -55℃~+105℃

盐雾时间 : 48H

2. 材料:

胶芯 : PBT, rated UL94V-0

接触点: 铜合金, 镀金1u"-30u"

铁壳 : SPCC, 前壳镀镍后壳镀锡

铜柱 : 铜合金, 镀镍

螺丝 : 铁合金, 镀镍

| 额定电流 | φA    | PCB孔φB |
|------|-------|--------|
| 10A  | Ø1.80 | Ø2.00  |
| 20A  | Ø2.80 | Ø3.00  |
| 30A  | Ø3.30 | Ø3.50  |
| 40A  | Ø3.80 | Ø4.00  |

| TOLERANCE TABLE |       |
|-----------------|-------|
| .0              | ±0.30 |
| .00             | ±0.20 |
| .000            | ±0.05 |

|                   |                         |                                                    |                 |       |        |
|-------------------|-------------------------|----------------------------------------------------|-----------------|-------|--------|
| APPROVED:         | DATE:                   | Ckmtw 深圳市灿科盟实业有限公司<br>CHANKLEMENT INDUSTRYCO., LTD |                 |       |        |
| CHECKED:          | DATE:                   | TITLE:<br>DWS-21W1M 公头 直插 全金 铆鱼叉锁螺丝                |                 |       |        |
| DRAWN:<br><br>LYF | DATE:<br><br>2024-01-13 | PART. NO.                                          | D-DWS021PM-F000 |       |        |
|                   |                         | UNIT                                               | mm              | SCALE | free   |
|                   |                         | FILE NO.                                           | Ckmtw-DWS-00021 | REV.  | A QT00 |