








Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)

额定电流	∅A	PCB孔∅B
10A	∅1.80	∅2.00
20A	∅2.80	∅3.00
30A	∅3.30	∅3.50
40A	∅3.80	∅4.00

说明:
1. 特性:
额定电压 : 500V AC MAX
小针额定电流 : 5A
大针额定电流 : 10A, 20A, 30A, 40A
接触电阻 : 30mΩ MAX.
绝缘电阻 : 3000MΩ MIN. at 500V DC
耐电压值 : 1000V AC RMS for 1minute
温度范围 : -55℃~+105℃
盐雾时间 : 48H
2. 材料:
胶芯 : PBT, rated UL94V-0
接触点: 铜合金, 镀金1u"-30u"
铁壳 : SPCC, 前壳电镀后壳镀锡
铜柱 : 铜合金, 镀镍
螺丝 : 铁合金, 镀镍

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	TITLE: DWS-5W1F 母头 直插 全金 铆鱼叉锁螺丝			
CHECKED:	DATE:				
DRAWN:	DATE:	PART. NO.	D-DWS005PF-F000	UNIT	mm
LYF	2024-01-13	FILE NO.	Ckmtw-DWS-00004	SCALE	free
		REV.	A	REV.	QT00

深圳市灿科盟实业有限公司
CKMTW CHANKLEMENT INDUSTRY CO., LTD