








UNC 4#40*2



Recommended P.C.B Layout (Top Side)
(PCB BOARD TOLERANCE ± 0.05)



说明:

1. 特性:

额定电压 : 500V AC MAX

小针额定电流 : 5A

大针额定电流 : 10A, 20A, 30A, 40A

接触阻抗 : 30m Ω MAX.

绝缘阻抗 : 3000M Ω MIN. at 500V DC

耐电压值 : 1000V AC RMS for 1Minute

温度范围 : -55 $^{\circ}$ C ~ +105 $^{\circ}$ C

盐雾时间 : 48H

2. 材料:

胶芯 : PBT, rated UL94V-0

接触点 : 铜合金, 镀金 1u"~30u"

铁壳 : SPCC, 前壳镀镍后壳镀锡

铜柱 : 铜合金, 镀锡

螺丝 : 铁合金, 镀镍

额定电流	ϕA	PCB孔 ϕB
10A	$\phi 1.80$	$\phi 2.00$
20A	$\phi 2.80$	$\phi 3.00$
30A	$\phi 3.30$	$\phi 3.50$
40A	$\phi 3.80$	$\phi 4.00$

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRY CO., LTD			
CHECKED:	DATE:	TITLE: DWS-9W4F 母头 直插 全金 铆鱼叉锁螺丝			
DRAWN: LYF	DATE: 2024-01-13	PART. NO.	D-DWS009PF-F000		
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-DWS-00016	REV.	A QT00

TOLERANCE TABLE	
.0	± 0.30
.00	± 0.20
.000	± 0.05