







额定电流	∅A	PCB孔∅
10A	∅1.80	∅2.00
20A	∅2.80	∅3.00
30A	∅3.30	∅3.50
40A	∅3.80	∅4.00



RECOMMENDED P.C.B LAYOUT (TOP VIEW)
TOLERANCES: $\pm 0.10\text{mm}$

TOLERANCE TABLE	
.0	± 0.30
.00	± 0.20
.000	± 0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD.					
CHECKED:	DATE:	TITLE: DWS-24W7F 母头 直插 全金 铆鱼叉锁螺丝					
DRAWN:	DATE:	PART. NO.		D-DWS024PF-F000			
		UNIT	mm	SCALE	free		
		FILE NO.	Ckmtw-DWS-00036		REV.	A	QT00
LYF	2024-01-13						