




Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE ± 0.05)

说明:

1. 特性:

额定电压 :500V AC MAX
大针额定电流 :10A, 20A, 30A, 40A
接触阻抗 :30m Ω MAX.
绝缘阻抗 :3000M Ω MIN. at 500V DC
耐电压值 :1000V AC RMS for 1Minute
温度范围 : -55 $^{\circ}$ C~+105 $^{\circ}$ C
盐雾时间 : 48H

2. 材料:

胶芯 : PBT, rated UL94V-0
接触点: 铜合金, 镀金1u"-30u"
铁壳 : SPCC, 前壳镀镍后壳镀锡
铜柱 : 铜合金, 镀镍
螺丝 : 铁合金, 镀镍

额定电流	ϕA	PCB孔 ϕB
10A	$\phi 1.80$	$\phi 2.00$
20A	$\phi 2.80$	$\phi 3.00$
30A	$\phi 3.30$	$\phi 3.50$
40A	$\phi 3.80$	$\phi 4.00$

TOLERANCE TABLE	
.0	± 0.30
.00	± 0.20
.000	± 0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD			
CHECKED:	DATE:	TITLE: DWS-3V3F 母头 直插 全金 铆鱼叉锁螺丝			
DRAWN: LYF	DATE: 2024-01-13	PART. NO.	D-DWS03VPF-F000		
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-DWS-00008	REV.	A QT00