





Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE $\pm$ 0.05)



说明:

1. 特性:

额定电压 :500V AC MAX

小针额定电流 :5A

大针额定电流 :10A, 20A, 30A, 40A

接触阻抗 :30m Ω MAX.

绝缘阻抗 :3000M Ω MIN. at 500V DC

耐电压值 :1000V AC RMS for 1Minute

温度范围 : -55 $^{\circ}$ C--+105 $^{\circ}$ C

盐雾时间 : 48H

2. 材料:

胶芯 : PBT, rated UL94V-0

接触点: 铜合金, 镀金1u"-30u"

铁壳 : SPCC, 前壳镀镍后壳镀锡

铜柱 : 铜合金, 镀镍

螺丝 : 铁合金, 镀镍

额定电流	ϕ A	PCB孔 ϕ B
10A	ϕ 1.80	ϕ 2.00
20A	ϕ 2.80	ϕ 3.00
30A	ϕ 3.30	ϕ 3.50
40A	ϕ 3.80	ϕ 4.00

TOLERANCE TABLE	
.0	$\pm$ 0.30
.00	$\pm$ 0.20
.000	$\pm$ 0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD			
CHECKED:	DATE:	TITLE: DWS-27W2M 公头 直插 全金 铆鱼叉锁螺丝			
DRAWN: LYF	DATE: 2024-01-13	PART. NO.		D-DWS027PM-F000	
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-DWS-00033	REV.	A QT00