



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE ± 0.05)



说明:

1. 特性:

额定电压 : 500V AC MAX

大针额定电流 :10A, 20A, 30A, 40A

接 触 阻 抗 : 30mΩ MAX.

绝 缘 阻 抗 :3000M Ω MIN. at 500V DC

耐电压值 :1000V AC RMS for 1Minute

温度范围：-55℃~+105℃

盐雾时间：48H

2. 材料:

胶 芯 : PBT, rated UL94V-0

接触点：铜合金，镀金1u"-30u"

铁壳：SPCC，前壳镀镍后壳镀锡

铜柱：铜合金，镀镍

螺 丝：铁合金，镀镍

额定电流	∅A	PCB孔∅
10A	∅1.80	∅2.00
20A	∅2.80	∅3.00
30A	∅3.30	∅3.50
40A	∅3.80	∅4.00

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD				
CHECKED:	DATE:	TITLE: DWS-2V2F 母头 直插 全金 铆鱼叉锁螺丝				
DRAWN: LYF	DATE: 2024-01-13	PART. NO.		D-DWS02VPF-F000		
		UNIT	mm	SCALE	free	 
		FILE NO.	Ckmtw-DWS-00040	REV.	A	QT00