



Common Mode Choke

TCK-181


Order Code	TCK-181
Inductance (each winding)	566 μ H $\pm$ 35% (at 100 kHz / 1 V)
Impedance (DCR)	50 m Ω max.
Rated Current	2 A max.
Rated Voltage	500 VDC max. (between windings)
Operating Temperature	-40°C to +105°C
RoHS Exemptions	No Exemptions
Overview Link	www.tracopower.com/overview/tck-181



Impedance Curve



Outline Dimensions



Dimensions [mm]	
A	11.5 max.
B	11.5 max.
C	8.8 max.
D	4.0 $\pm$ 0.3
E	7.62 $\pm$ 0.2
F	7.62 $\pm$ 0.2
G	$\varnothing$ 0.6 $\pm$ 0.1

All specifications valid at +25°C, unless otherwise stated.