



USB2.0 A Male to B Male Printer Cable

Faster&More Stable

USB2.0 Printer Cable



High speed
480Mbps

Tinned
Copper


Optional
Ferrite core

Computer connect printer

Signal transmission is more stable



1-5m Length Optional





USB2.0 High Speed Printing

Theoretical speed up to 480Mbps

USB B Square Interface

Connect sound card/external drive



Anti-interference Protection

Aluminum Foil+Metal Braided
Signal transmission is more stable



Tinned Copper Core

Improve the quality of print



Different Style

No ferrite core
Black/White
1m-3m



Double ferrite cores
Black/White
5m



PVC Jacket

Flexible and durable





Plug And Play

Apply to multiple types of equipment



Drive



Sound Card



Fax machine



Printer



Scanner

Product Parameters

Brand: Vention

Name: USB2.0 Print Cable

Model: VAS-A16

Appearance Color: Black/White

Interface Type: USB A male; USB B male

Version: USB 2.0

Theoretical Speed: 480Mbps

Interface Process: Nickel plated

Conductor Material: BC

Cable Shielding: Aluminum foil+metal braided

Jacket: PVC


AWG: 24+28AWG

Cable OD: 4.5mm

Cable Length: 1m-5m

Product Warranty: One year

Package: PE bag



Length	Art.No.	EAN Code
1m	VAS-A16-B100	6922794717572
1.5m	VAS-A16-B150	6922794732612
2m	VAS-A16-B200	6922794717589
3m	VAS-A16-B300	6922794717596
5m	VAS-A16-B500	6922794717602
8m	VAS-A16-B800	6922794717619
10m	VAS-A16-B1000	6922794732605



Package Contents

USB Cable x 1

Packaging Information

Packing Dimension	mm
Packing Weight	kg
Carton Dimension	48*29*30mm
Carton Qty	200pcs(1m) 200pcs(1.5m) 150pcs(2m) 100pcs(3m) 70pcs(5m) 50pcs(8m) 46pcs(10m)
Carton Weight	10kg
Package	PE bag

www.ventioncable.com