




建议胶圈尺寸



SPECIFICATION:

1.Material:

HOUSING&MOLDING:
HIGH TEMPERATURE RESISTANT PLASTIC,
UL94 V-0

CONTACTS:COPPER ALLOY T=0.15mm
IDDL CLIP:SUS301-1/2H,T=0.15mm
SHELL-1:SUS304, T=0.30mm
SHELL-2:SUS304, T=0.20mm

2.Mechanical:






2.1.Mating force:0.5~2.0kgf.
2.2.UNMATING FORCE:0.8~2.0kgf.
0.6~2.0kgf AFTER DURABILITY TEST;
2.3.Durability:10000 Cycles;

3.Electrical:


3.1.Current Rating:3A Max.;
3.2.Voltage Rating:20V Max.;
3.3.Dielectric Withstanding voltage:100VAc;
3.4.Contact resistance:40m Ohms Max.;
3.5.Insulation Resistance:100M Ohms Min.;

4.Environmental:

4.1.Operating temperature:-40°C~+85°C;
4.2.Wetting Temperature:265±5°C,5±0.5s



RECOMMENDED P.C.B. LAYOUT (T:1.0~1.2mm)
TOLERANCE UNSPECIFIED ±0.05mm



SECTION A-A

A5	CC1	B5	CC2
A9	VBUS	B9	VBUS
A12	GND	B12	GND
PIN	SIGNAL	PIN	SIGNAL



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2' X.X' ±0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: USB TYPE C 防水母座6P 板上型SMT 带柱四脚
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW542-USBC06-790B
	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2407281201
SCALE:1:1 SIZE: A4			SHEET NO. 1 OF 1