








建议胶圈尺寸



SPECIFICATION:

1.Material:

HOUSING&MOLDING:
HIGH TEMPERATURE RESISTANT PLASTIC,
UL94 V-0

CONTACTS: COPPER ALLOY T=0.15mm

IDLE CLIP: SUS301-1/2H, T=0.15mm

SHELL-1: SUS304, T=0.30mm

SHELL-2: SUS304, T=0.20mm

2.Mechanical:

2.1.Mating force: 0.5~2.0kgf.

2.2.UNMATING FORCE: 0.8~2.0kgf.

0.6~2.0kgf AFTER DURABILITY TEST;

2.3.Durability: 10000 Cycles;

3.Electrical:

3.1.Current Rating: 3A Max.;

3.2.Voltage Rating: 20V Max.;

3.3.Dielectric Withstanding voltage: 100VAc;

3.4.Contact resistance: 40m Ohms Max.;


3.5.Insulation Resistance: 100M Ohms Min.;

4.Environmental:


4.1.Operating temperature: -40°C~+85°C;

4.2.Wetting Temperature: 265±5°C, 5±0.5s

A5	CC1	B5	CC2
A9	VBUS	B9	VBUS
A12	GND	B12	GND
PIN	SIGNAL	PIN	SIGNAL



RECOMMENDED P.C.B. LAYOUT (T: 1.0~1.2mm)
TOLERANCE UNSPECIFIED ±0.05mm



SECTION A-A



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2' X.X' ±0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: USB TYPE C 防水母座6P 板上型SMT 带柱两脚
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW541-USBC06-790B
	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.
			DRAW NO: HYC-2407281154
			SHEET NO. 1 OF 1