





SECTION A-A



SPECIFICATIONS

Material:

Insulator:Glass filled PBT (UL94V-0),Black

Contacts:Brass

Plating:Grod Flash

Electrical Charactristics:

Contact Resistance:20mΩ Max.

Insulator Resistance:1000MΩ Min.

Withstanding Voltage:AC 500V

Currrnt Rating:3 AMP

Operating Temperature:-40℃ to +105℃

Insertion force: 0.6±0.2kgf

Extraction force: 0.25±0.1kgf



深圳市华宇创精密电子有限公司

TOLERANCE:

X.X ±0.30

X.XX ±0.25

X.XXX ±0.15

X.' ±2' X.X' ±0.5'



UNIT: mm [inch]

SCALE:1:1 SIZE: A4

DRAWN BY :

陈一鸣

DATE :

2014-02-23

PART NAME:

2.54PH 开口短路帽

CHECKED BY:

马跃

DATE :

2014-02-23

PART NO.

HYCW04-TX02-254B

MOLD NO.

APPROVED BY:

邱国夷

DATE :

2014-02-23

DRAW NO:

HYC-1709061456

SHEET NO.

1 OF 1