




SECTION A-A



SPECIFICATIONS

Material:

Insulator:Glass filled PBT (UL94V-0),Black

Contacts:Brass

Plating: Au or Sn over 50u'' Ni

Electrical Charactristics:

Contact Resistance:20mΩ Max.

Insulator Resistance:1000MΩ Min.

Withstanding Voltage:AC 500V

Currrent Rating:3 AMP

Operating Temperature:-40℃ to +105℃



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2' X.X' ±0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 2.54PH 闭口短路帽	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	HYCW03-TX02-254B
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱国夷	DATE : 2014-02-23	DRAW NO:	HYC-1709061454
			SHEET NO.	1 OF 1