



E		F	
DIMENSION(尺寸)			
No of conductors(导体数目)	N	YY	
Pitch (间距)	▲ P	1. 0	±0. 05
Span (总间距)	▲ SP	1. 0*(10-1)	±0. 07
Width (宽度)	▲ W	1. 0*(10+1)	±0. 08
Margin (边距)	▲ M	1. 0	±0. 10
	/	/	/
Total length(总长)	▲ TL	100	±2. 0
Insulator length(绝缘段长)	IL	92	/
Insert Thickness(插接端厚度)	T	0. 30	±0. 05
Surface Thickness(线身厚度)	ST	0. 12	±0. 05
Strip length (裸铜长度)	▲ S1	4. 00	±0. 5
	▲ S2	4. 00	±0. 5
Supporting Tape length (补强板长度)	B1	8. 00	±1. 5
	B2	8. 00	±1. 5
Strip Slant (线口倾斜)	A1	≤0. 3	
Punch Slant (冲孔倾斜)	A2	≤0. 3	



Material List (辅料清单)			
NO	ITEM(项目)	SPEC(规格)	QTY(数量)
1			
2			
3			
4			
5			
6			



STRUCTURE (构造)				
NO	ITEM (项目)	SPECIFICATION (规格)		REMARK (备注)
1	INSULATION (胶膜)	Printed 印字 (43um)		
		AWM 20706 150C 60V VW-1		
		White 白色 (43um)	/	
2	SUPPORTING TAPE (补强板)	Blue 蓝色 (225um)	/	
3	CONDUCTOR 导体	Thickness (厚度)	0.035	±0.005
		Width (宽度)	0.65	±0.03
		PLATED (电镀)	Sn (40 μ " 锡)	MIN
4	CONDUCTOR 导体镀层	PLATED (电镀)	/	/



SHENZHEN MINTRON TECHNOLOGY CO.,LTD.			
品名 (ITEM)	制膜 (DB)		
1.0 FCC同向排线-10P TL=100mm	校对 (CHECK)	Kenny	
料号 (DWG.NO)	审核 (APPD)	Thomas	
MTA-DT10-0100C-4/4/8/8	Dwain		
比例 (SCALE)	单位 (UNITS)	张数 (SHEET)	SIZE REV
1:1	mm	1 OF 1	A4 A
F		F	