





- NOTES:
- 1. Rated voltage: 250V AC/DC
 - 2. Rated current: 3A AC/DC
 - 3. Contact resistance: $\leq 20 \text{ m}\Omega$
 - 4. Insulation resistance: $\geq 1000 \text{ M}\Omega$
 - 5. Withstand voltage: 1000V AC/minute
 - 6. Ambient temperature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
 - 7. Material: Nylon UL94V-0 750°C
 - 8. Pin Materials: Brass/Tin-Plated.

Circuits	Product name	Dimension mm			Circuits	Product name	Dimension mm		
		A	B	C			A	B	C
2	TJC3-2A-750	2.50	7.50	6.00	10	TJC3-10A-750	22.50	27.50	26.00
3	TJC3-3A-750	5.00	10.00	8.50	11	TJC3-11A-750	25.00	30.00	28.50
4	TJC3-4A-750	7.50	12.50	11.00	12	TJC3-12A-750	27.50	32.50	31.00
5	TJC3-5A-750	10.00	15.00	13.50	13	TJC3-13A-750	30.00	35.00	33.50
6	TJC3-6A-750	12.50	17.50	16.00	14	TJC3-14A-750	32.50	37.50	36.00
7	TJC3-7A-750	15.00	20.00	18.50	15	TJC3-15A-750	35.00	40.00	38.50
8	TJC3-8A-750	17.50	22.50	21.00	-	-	-	-	-
9	TJC3-9A-750	20.00	25.00	23.50	20	TJC3-20A-750	47.50	52.50	51.00

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD	
.X: ± 0.25	X°: $\pm 3.0^{\circ}$	PRODUCT NAME:	TITLE: 2.50 mm Pitch Wire To Board Wafer
.XX: ± 0.15	.X°: $\pm 2.0^{\circ}$	DR: Chen Quan Long	DATE: 19/08/01
.XXX: ± 0.01	.XX°: $\pm 1.0^{\circ}$	CHKD: Wu Hui	DATE: 19/08/01
FINISH:		APPD: Ren An De	DATE: 19/08/01
DRAWING NO: GC-TJC3-A-750			




REV.	REVISION DESCRIPTION	DATE	APPD

- NOTES:
- 1. Rated voltage: 250V AC/DC
 - 2. Rated current: 3A AC/DC
 - 3. Contact resistance: $\leq 20\text{ m}\Omega$
 - 4. Insulation resistance: $\geq 1000\text{ M}\Omega$
 - 5. Withstand voltage: 1000V AC/minute
 - 6. Ambient temperature: $-40^{\circ}\text{C}\sim +105^{\circ}\text{C}$
 - 7. Material : Nylon UL94V-0 750 $^{\circ}\text{C}$
 - 8. Pin Materials : Brass/Tin-Plated.

Circuits	Product name	Dimension mm			Circuits	Product name	Dimension mm		
		A	B	C			A	B	C
2	TJC3-2A-Z-750	2.50	7.50	6.00	10	TJC3-10A-Z-750	22.50	27.50	26.00
3	TJC3-3A-Z-750	5.00	10.00	8.50	11	TJC3-11A-Z-750	25.00	30.00	28.50
4	TJC3-4A-Z-750	7.50	12.50	11.00	12	TJC3-12A-Z-750	27.50	32.50	31.00
5	TJC3-5A-Z-750	10.00	15.00	13.50	13	TJC3-13A-Z-750	30.00	35.00	33.50
6	TJC3-6A-Z-750	12.50	17.50	16.00	14	TJC3-14A-Z-750	32.50	37.50	36.00
7	TJC3-7A-Z-750	15.00	20.00	18.50	15	TJC3-15A-Z-750	35.00	40.00	38.50
8	TJC3-8A-Z-750	17.50	22.50	21.00	-	-	-	-	-
9	TJC3-9A-Z-750	20.00	25.00	23.50	20	TJC3-20A-Z-750	47.50	52.50	51.00


GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD	
.X: ± 0.25	X $^{\circ}$: $\pm 3.0^{\circ}$	PRODUCT NAME: DL25001(TJC3)-A-Z-750	TITLE: 2.50 mm Pitch Wire To Board Wafer
.XX: ± 0.15	.X $^{\circ}$: $\pm 2.0^{\circ}$	DR:Chen Quan Long	DATE:19/08/01
.XXX: ± 0.01	.XX $^{\circ}$: $\pm 1.0^{\circ}$	CHKD: Wu Hui	DATE:19/08/01
FINISH:		APPD:Ren An De	DATE:19/08/01
DRAWING NO:			



- NOTES:
- 1. Rated voltage: 250V AC.DC
 - 2. Rated current: 3A AC DC
 - 3. Contact resistance: $\leq 20\text{ m}\Omega$
 - 4. Insulation resistance: $\geq 1000\text{ M}\Omega$
 - 5. Withstand voltage: 1000V AC/minute
 - 6. Ambient temperature: $-40^{\circ}\text{C}\sim +105^{\circ}\text{C}$
 - 7. Material : Nylon UL94V-0 750°C
 - 8. Pin Materials : Brass/Tin-Plated.

Circuits	Product name	Dimension mm			Circuits	Product name	Dimension mm		
		A	B	C			A	B	C
2	TJC3-2AS-750	2.50	7.50	6.00	10	TJC3-10AS-750	22.50	27.50	26.00
3	TJC3-3AS-750	5.00	10.00	8.50	11	TJC3-11AS-750	25.00	30.00	28.50
4	TJC3-4AS-750	7.50	12.50	11.00	12	TJC3-12AS-750	27.50	32.50	31.00
5	TJC3-5AS-750	10.00	15.00	13.50	13	TJC3-13AS-750	30.00	35.00	33.50
6	TJC3-6AS-750	12.50	17.50	16.00	14	TJC3-14AS-750	32.50	37.50	36.00
7	TJC3-7AS-750	15.00	20.00	18.50	15	TJC3-15AS-750	35.00	40.00	38.50
8	TJC3-8AS-750	17.50	22.50	21.00	-	-	-	-	-
9	TJC3-9AS-750	20.00	25.00	23.50	20	TJC3-20AS-750	47.50	52.50	51.00

GENERAL TOLERANCES (UNLESS SPECIFIED)				ZHE JIANG DELI CONNECTORS CO.,LTD			
.X: ± 0.25		X° : ± 3.0°		PRODUCT NAME: DL25001 (TJC3)-AS-750		TITLE: 2.50 mm Pitch Wire To Board Wafer	
.XX: ± 0.15		.X° : ± 2.0°		DR:Chen Quan Long		DATE:19/08/01	
.XXX: ± 0.01		.XX° : ± 1.0°		FINISH:		PART NO:	
DRAWING NO:		APPD:Ren An De		DATE:19/08/01		SCALE: N/A	
						PAGE: 1/1	
						UNITS: mm	
						REV.: A	




REV.	REVISION DESCRIPTION	DATE	APPD

- NOTES:
- 1. Rated voltage: 250V AC.DC
 - 2. Rated current: 3A AC DC
 - 3. Contact resistance: ≤20 mΩ
 - 4. Insulation resistance: ≥1000 MΩ
 - 5. Withstand voltage: 1000V AC/minute
 - 6. Ambient temprature: -40℃ ~ +105℃
 - 7. Material : Nylon UL94V-0 750℃
 - 8. Pin Materials : Brass/Tin-Plated.

Circuits	Product name	Dimension mm			Circuits	Product name	Dimension mm		
		A	B	C			A	B	C
2	TJC3-2AW-750	2.50	7.50	6.00	10	TJC3-10AW-750	22.50	27.50	26.00
3	TJC3-3AW-750	5.00	10.00	8.50	11	TJC3-11AW-750	25.00	30.00	28.50
4	TJC3-4AW-750	7.50	12.50	11.00	12	TJC3-12AW-750	27.50	32.50	31.00
5	TJC3-5AW-750	10.00	15.00	13.50	13	TJC3-13AW-750	30.00	35.00	33.50
6	TJC3-6AW-750	12.50	17.50	16.00	14	TJC3-14AW-750	32.50	37.50	36.00
7	TJC3-7AW-750	15.00	20.00	18.50	15	TJC3-15AW-750	35.00	40.00	38.50
8	TJC3-8AW-750	17.50	22.50	21.00	-	-	-	-	-
9	TJC3-9AW-750	20.00	25.00	23.50	20	TJC3-20AW-750	47.50	52.50	51.00

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD	
.X: ± 0.25	.X° : ± 3.0°	PRODUCT NAME: DL25001 (TJC3)-AW-750	TITLE: 2.50 mm Pitch Wire To Board Wafer
.XX: ± 0.15	.X° : ± 2.0°	DR:Chen Quan Long	DATE:19/08/01
.XXX: ± 0.01	.XX° : ± 1.0°	CHKD: Wu Hui	DATE:19/08/01
FINISH:		APPD:Ren An De	DATE:19/08/01
DRAWING NO:			



REV.	REVISION DESCRIPTION	DATE	APPD

A


B

C

D

E

F



NOTES:

1. Rated voltage: 250V AC.DC
2. Rated current: 3A AC DC
3. Contact resistance: ≤20 mΩ
4. Insulation resistance: ≥1000 MΩ
5. Withstand voltage: 1000V AC/minute
6. Ambient temprature: -40℃ ~ +105℃
7. Material : Nylon UL94V-0 750℃
8. Pin Materials : Brass/Tin-Plated.

A


B

C

D

E

F




Circuits	Product name	Dimension mm			Circuits	Product name	Dimension mm		
		A	B	C			A	B	C
2	TJC3-2AWT-750	2.50	7.50	6.00	10	TJC3-10AWT-750	22.50	27.50	26.00
3	TJC3-3AWT-750	5.00	10.00	8.50	11	TJC3-11AWT-750	25.00	30.00	28.50
4	TJC3-4AWT-750	7.50	12.50	11.00	12	TJC3-12AWT-750	27.50	32.50	31.00
5	TJC3-5AWT-750	10.00	15.00	13.50	13	TJC3-13AWT-750	30.00	35.00	33.50
6	TJC3-6AWT-750	12.50	17.50	16.00	14	TJC3-14AWT-750	32.50	37.50	36.00
7	TJC3-7AWT-750	15.00	20.00	18.50	15	TJC3-15AWT-750	35.00	40.00	38.50
8	TJC3-8AWT-750	17.50	22.50	21.00	-	-	-	-	-
9	TJC3-9AWT-750	20.00	25.00	23.50	20	TJC3-20AWT-750	47.50	52.50	51.00

GENERAL TOLERANCES (UNLESS SPECIFIED)				ZHE JIANG DELI CONNECTORS CO.,LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DL25001(TJC3)-AWT-750		TITLE: 2.50 mm Pitch Wire To Board Wafer		PART NO:	
.XX: ± 0.15	.X° : ± 2.0°	DR:Chen Quan Long		DATE:19/08/01		SCALE: N/A	
.XXX: ± 0.01	.XX° : ± 1.0°	CHKD: Wu Hui		DATE:19/08/01		PAGE: 1/1	
FINISH:		APPD:Ren An De		DATE:19/08/01		UNITS: mm	
DRAWING NO:						REV.: A	


7		8	
REV.	REVISION DESCRIPTION	DATE	APPD

- NOTES:
1. Rated voltage: 250V AC/DC
 2. Rated current: 3A AC/DC
 3. Contact resistance: $\leq 20 \text{ m}\Omega$
 4. Insulation resistance: $\geq 1000 \text{ M}\Omega$
 5. Withstand voltage: 1000V AC/minute
 6. Ambient temperature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
 7. Material : Nylon UL94V-0 750°C
 8. Pin Materials : Brass/Tin-Plated.



Circuits	Product name	Dimension mm			Circuits	Product name	Dimension mm		
		A	B	C			A	B	C
2	TJC3-2AWF-750	2.50	7.50	6.00	10	TJC3-10AWF-750	22.50	27.50	26.00
3	TJC3-3AWF-750	5.00	10.00	8.50	11	TJC3-11AWF-750	25.00	30.00	28.50
4	TJC3-4AWF-750	7.50	12.50	11.00	12	TJC3-12AWF-750	27.50	32.50	31.00
5	TJC3-5AWF-750	10.00	15.00	13.50	13	TJC3-13AWF-750	30.00	35.00	33.50
6	TJC3-6AWF-750	12.50	17.50	16.00	14	TJC3-14AWF-750	32.50	37.50	36.00
7	TJC3-7AWF-750	15.00	20.00	18.50	15	TJC3-15AWF-750	35.00	40.00	38.50
8	TJC3-8AWF-750	17.50	22.50	21.00	-	-	-	-	-
9	TJC3-9AWF-750	20.00	25.00	23.50	20	TJC3-20AWF-750	47.50	52.50	51.00

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD	
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DL25001 (TJC3)-AWF-750	TITLE: 2.50 mm Pitch Wire To Board Wafer
.XX: ± 0.15	.X° : ± 2.0°	DR:Chen Quan Long	DATE:19/08/01
.XXX: ± 0.01	.XX° : ± 1.0°	DATE:19/08/01	PART NO:
FINISH:		CHKD: Wu Hui	DATE:19/08/01
DRAWING NO:		APPD:Ren An De	DATE:19/08/01
		SCALE: N/A	PAGE: 1/1
		UNITS: mm	REV.: A



REV.	REVISION DESCRIPTION	DATE	APPD

NOTES

Available in 02 through 20 Circuits.

Match with DL25001 series housing


Material : Nylon UL94V-0 750°C.

Accepts DL25001-T Crimp Terminal.

Circuits	Dimension mm			Circuits	Dimension mm		
	A	B	C		A	B	C
2	2.50	5.70	7.30	12	27.50	30.70	32.30
3	5.00	8.20	9.80	13	30.00	33.20	34.80
4	7.50	10.70	12.30	14	32.50	35.70	37.30
5	10.00	13.20	14.80	15	35.00	38.20	39.80
6	12.50	15.70	17.30	16	37.50	40.70	42.30
7	15.00	18.20	19.80	17	40.00	43.20	44.80
8	17.50	20.70	22.30	18	42.50	45.70	47.30
9	20.00	23.20	24.80	19	45.00	48.20	47.30
10	22.50	25.70	27.30	20	47.50	50.70	52.30
11	25.00	28.20	29.80				

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO ., LTD	
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME:	TITLE:
.XX: ± 0.15	.X° : ± 2.0°	DL25001 (TJC3)-Y-750	2.50 mm Pitch Housing
.XXX: ± 0.01	.XX° : ± 1.0°	DR:Chen Quan Long	DATE:19/08/01
FINISH:		CHKD: Wu Hui	DATE:19/08/01
DRAWING NO:		APPD:Ren An De	DATE:19/08/01
			SCALE: N/A
			PAGE: 1/1
			UNITS: mm
			REV.: A

REV.	REVISION DESCRIPTION	DATE	APPD



NOTES

Used in DL25001-Y Series Housing.
Accepts AWG #28~22 Wire Range.


0.08~ 0.33 mm² .

Insulation O.D.=1.2~1.9 mm.


Material : Phosphor Bronze .

Finish: Tin plated.


Thickness: 0.2 mm.



SECTION A-A




SECTION B-B



SECTION C-C

GENERAL TOLERANCES (UNLESS SPECIFIED)				ZHE JIANG DELI CONNECTORS CO .,LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME:		TITLE:			
.XX: ± 0.15	.X° : ± 2.0°	DL25001 (TJC3)-T		2.50 mm Pitch Crimp Terminal			
.XXX: ± 0.01	.XX° : ± 1.0°	DR:Chen Quan Long	DATE:19/08/01	PART NO:			
FINISH:		CHKD: Wu Hui	DATE:19/08/01	SCALE: N/A		PAGE: 1/1	
DRAWING NO:		APPD:Ren An De	DATE:19/08/01	UNITS: mm		REV. : A	



REV.	REVISION DESCRIPTION	DATE	APPD

NOTES

Used in DL25001-Y Series Housing.
Accepts AWG #24~20 Wire Range.
Material : Phosphor Bronze .
Finish: Tin plated.
Thickness: 0.2 mm.

GENERAL TOLERANCES (UNLESS SPECIFIED)				ZHE JIANG DELI CONNECTORS CO .,LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME:		TITLE:			
.XX: ± 0.15	.X° : ± 2.0°	DL25001 (TJC3) -T-G		2.50 mm Pitch Crimp Terminal			
.XXX: ± 0.01	.XX° : ± 1.0°	DR:Chen Quan Long	DATE:19/08/01	PART NO:			
FINISH:		CHKD: Wu Hui	DATE:19/08/01	SCALE: N/A		PAGE: 1/1	
DRAWING NO:		APPD:Ren An De	DATE:19/08/01	UNITS: mm		REV.: A	