



REV.	DATE	ECN NO.	MODIFICATION	APPROVER
A0	2019.12.21	/	NEW	Jason
A1	2022.10.13	RD00322101301	增加管控尺寸	Abel



Specifications:

Material:

- Housing: Plastic particles, 白色/米色/黑色 UL94V-0
- Contact: Brass. Tin plated over Nickel plated underall.

Electrical:



- Current Rating: 3.0A
- Voltage Rating: 250V
- Contact Resistance: 20mΩ MAX
- Dielectric Withstanding Voltage: 1000V AC
- Insulation Resistance: 1000MΩ MIN

Environment characteristics:


- Operating Temperature: -25°C~+85°C

Major Dimension:▼

Lead free and ROHS compliant product.



CKT	A	B	CKT	A	B
2	2.5	7.5	10	22.5	27.5
3	5.0	10.0	11	25.0	30.0
4	7.5	12.5	12	27.5	32.5
5	10.0	15.0	13	30.0	35.0
6	12.5	17.5	14	32.5	37.5
7	15.0	20.0	15	35.0	40.0
8	17.5	22.5	16	37.5	42.5
9	20.0	25.0			



适用线路板 (PCB LAYOUT)

GENERAL TOLERANCE				UNITS mm	NAME(INTENDED USE) WF	ATOM® 深圳市爱特姆科技有限公司 SHENZHEN ATOM TECHNOLOGY CO., LTD.			
SELECT	✓					PART NO.(INTENDED USE) WF250**-07***	TITLE: Customer Drawing For Wafer2.5mm XP DIP 180° 带扣 无K脚		
TOL.	1	2	3	MAT'L	APPD: Abel		DWG NO.: ATOM-A06819		
X.XXX	±0.10	±0.15	±0.20			FINISH	CHKD: TOM		SCALE
X.XX	±0.15	±0.20	±0.25	Q'TY	DR: Ling				1:1
X.X	±0.20	±0.25	±0.30						
X.	±0.25	±0.30	±0.50						
ANGLE	±2°								