


		D		E	
REV.	DESCRIPTION	ECN NO.	NAME	DATE	



SPECIFICATIONS

Current Rating:0.75 Amps

Withstanding Voltage:AC 500V

Insulation Resistance:1000MΩ Min

Contact Resistance: 20mΩ Max

Operation Temperature: -40° to $+105^{\circ}$

Insulator Material: Polyester (UL94V-0)



Contact Material: Phosphor bronze

Standard: PA6T

Contact Plating:Gold Flash

Max.Processing Temp:240°C for30-60seconds

(260°C for 5 seconds)



RECOMMEND P.C.B LAYOUT

PCB TOLERANCE: ± 0.05 (TOP VIEW)

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD					BXCONN [®]		
DIM. x. x.x x.xx GENERAL ANGLE: x° x.x' x.xx"		TOL. ±0.30 ±0.20 ±0.10 ±5° ±1° ±0.5°		TITLE: 1.0FH H2.0 1xnPin 180度 W1.5 U型 PC2.0 6T					
		DWG. NO.: AM-PM1.0-V11-1*NP			CHECKED: MAX				
		PART NO.: AM-PM1.0-V11-1*NP			DRAWN: ELLA				
		UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL		