


		D		E	
REV.	DESCRIPTION	ECN NO.	NAME	DATE	



SPECIFICATIONS

Current Rating:0.75 Amps

Withstanding Voltage:AC 500V

Insulation Resistance:1000MΩ Min

Contact Resistance: 20mΩ Max

Operation Temperature: -40° to $+105^{\circ}$



Insulator Material: Polyester (UL94V-0)

Contact Material: Phosphor bronze

Standard:PA6T

Contact Plating:Gold Flash

Max.Processing Temp:240°C for30-60seconds
(260°C for5seconds)



RECOMMEND P.C.B LAYOUT

PCB TOLERANCE: ± 0.05 (TOP VIEW)

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD					BXCONN [®]	
DIM. TOL. x. ±0.30 x.x ±0.20 x.xx ±0.10 GENERAL ANGLE: x° ±5° x' ±1° x.xx' ±0.5°		TITLE: 1.0FH H2.0 1xPin SMT W1.5 U型 PC2.8 PB2.3 6T (左前右后)						
		DWG. NO.: AM-PM1.0-V14-1*NP			CHECKED: MAX			
		PART NO.: AM-PM1.0-V14-1*NP			DRAWN: ELLA			
		UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL	