







|                                             |  |  |                                                               |        |            |
|---------------------------------------------|--|--|---------------------------------------------------------------|--------|------------|
| TITLE<br>SFP+ 2X8 CAGE+CONNECTOR            |  |  | CND-tek 深圳磁联达电子有限公司<br>Shen zhen cnd-tek Electronics Co., Ltd |        |            |
| PART NO.<br>SFP+ UE86-K8627-10321 2x8YD-CND |  |  | GENERAL TOLERANCE                                             |        | UNIT:MM    |
| APPROVE                                     |  |  | .X±0.20                                                       | .X±1°  | SCALE: 1:1 |
| CHECK                                       |  |  | .XX±0.15                                                      | .XX±5° |            |
| DRAW                                        |  |  | .XXX±0.10                                                     |        | SHEET:2/4  |
| QG.CHEN                                     |  |  |                                                               |        |            |
| SL.WANG                                     |  |  |                                                               |        | REV:A      |
| X.YAN                                       |  |  |                                                               |        |            |



Technical drawing of a circuit board layout showing dimensions and component placement for Circuit #1 Top and Bottom Modules.

**Dimensions (mm):**

- Overall width: 11.00
- Overall height: 6.52
- Top module height: 3.67, 2.28, 0.73
- Bottom module height: 0.65, 2.20, 3.59, 5.14
- Vertical spacing (left): 7.60, 7.20, 6.80, 6.40, 3.80, 1.70, 1.60 TYP.
- Vertical spacing (right): 1.70, 0.98, 0.65, 2.20, 3.59, 5.14, 6.52


**Component Placement:**


- CIRCUIT #1 TOP MODULE:** Indicated by a hatched area and a circle with a cross.
- CIRCUIT #1 BOTTOM MODULE:** Indicated by a hatched area and a circle with a cross.
- Drill Holes:**
  - Ø0.46 ± 0.05 TYP (Ø0.57 DRILL) (Ø0.88 PAD)
  - Ø0.100 ± 0.012 A/B
  - Ø1.85 ± 0.05 (2 PLACES)

**Other Labels:**

- REF. (Reference)
- B- (Bottom)
- A- (Top)

TERMINAL TAIL PATTERN

|                                             |         |       |                                                                                      |        |                                                                                       |           |          |
|---------------------------------------------|---------|-------|--------------------------------------------------------------------------------------|--------|---------------------------------------------------------------------------------------|-----------|----------|
| TITLE<br>SFP+ 2X8 CAGE+CONNECTOR            |         |       | <div>CND-tek</div> <div>深圳磁联达电子有限公司<br/>Shen zhen cnd-tek Electronics Co., Ltd</div> |        |                                                                                       |           |          |
| PART NO.<br>SFP+ UE86-K8627-10321 2x8YD-CND |         |       | GENERAL TOLERANCE                                                                    |        |  | UNIT:MM   | SIZE: A4 |
| APPROVE                                     | CHECK   | DRAW  | .X±0.20                                                                              | .X±1°  | SCALE: 1:1                                                                            | SHEET:3/4 | REV:A    |
|                                             |         |       | .XX±0.15                                                                             | .XX±5° |                                                                                       |           |          |
| QG.CHEN                                     | SL.WANG | X.YAN | XXX+0.10                                                                             |        |                                                                                       |           |          |



|                                             |         |       |                                                                                      |        |            |           |          |
|---------------------------------------------|---------|-------|--------------------------------------------------------------------------------------|--------|------------|-----------|----------|
| TITLE<br>SFP+ 2X8 CAGE+CONNECTOR            |         |       | <div>CND-tek</div> <div>深圳磁联达电子有限公司<br/>Shen zhen cnd-tek Electronics Co., Ltd</div> |        |            |           |          |
| PART NO.<br>SFP+ UE86-K8627-10321 2x8YD-CND |         |       | GENERAL TOLERANCE                                                                    |        |            | UNIT:MM   | SIZE: A4 |
| APPROVE                                     | CHECK   | DRAW  | .X±0.20                                                                              | .X±1°  | SCALE: 1:1 | SHEET:4/4 | REV:A    |
| QG.CHEN                                     | SL.WANG | X.YAN | .XX±0.15                                                                             | .XX±5° |            |           |          |
|                                             |         |       | .XXX±0.10                                                                            |        |            |           |          |