











RECOMMENDED PCB LAYOUT – COMPONENT SIDE
RECOMMENDED PCB THICKNESS : 2.36MM(.093 INCH)
(MINIMUM PCB THICKNESS : 1.57)

THE ENTIRE AREA OF THE CONNECTOR FOOTPRINT
TO BE CONSIDERED THE KEEP OUT AREA FOR COMPONENTS
THIS AREA IS INDICATED BY THE DASHED LINE

TITLE SFP 2X2 CAGE+CONNECTOR			CND-tek 深圳磁联达电子有限公司 Shen zhen cnd-tek Electronics Co., Ltd		
PART NO. SFP UE86-K2127-10321 2X2YD-CND			GENERAL TOLERANCE		UNIT:MM
APPROVE	CHECK	DRAW	.X±0.20	.X±1*	SCALE: 1:1
			.XX±0.15	.XX±5*	SHEET:2/4
			.XXX±0.10		REV:A




DETAIL-KEEPOUT ZONES



TERMINAL TAIL PATTERN

THE HATCHED AREA IN THIS VIEW INDICATES ZONES THAT ARE OCCUPIED BY THE PLASTIC HOUSING THAT SEATS AGAINST THE PCB AND BY THE VERTICAL METAL CAGE WALL THAT STOPS JUST SHORT OF THE PCB

TITLE SFP 2X2 CAGE+CONNECTOR			CND-tek 深圳磁联达电子有限公司 Shen zhen cnd-tek Electronics Co., Ltd		
PART NO. SFP UE86-K2127-10321 2X2YD-CND			GENERAL TOLERANCE		UNIT:MM
APPROVE	CHECK	DRAW	.X±0.20	.X±1°	SCALE: 1:1
			.XX±0.15	.XX±5°	SHEET:3/4
			.XXX±0.10		REV:A



TITLE SFP 2X2 CAGE+CONNECTOR			CND-tek 深圳磁联达电子有限公司 Shen zhen cnd-tek Electronics Co., Ltd		
PART NO. SFP UE86-K2127-10321 2X2YD-CND			GENERAL TOLERANCE		UNIT:MM
APPROVE	CHECK	DRAW	.X±0.20	.X±1°	SCALE: 1:1
			.XX±0.15	.XX±5°	SHEET:4/4
			.XXX±0.10		REV:A