





REV	DESCRIPTION OF CHANGE	REVIEWED BY	ISSUE DATE
A	FIRST ISSUE	X.YAN	2021-08-01


NOTES:
MATERIAL:
CAGE ASSEMBLY: COPPER ALLOY(C7701),NIKCEL PLATED
EMI SPRING: COPPER ALLOY(C5191),NIKCEL PLATED
LIGHT PIPE: POLYCARBONATE, UL94 V-0
HOUSING : POLYCARBONATE, UL94 V-0
CONNECTOR:
PLASTIC HOUSING: HIGH TEMPERATURE LCP, UL94 V-0.
SPRING: STAINLESS STEEL, THICKNESS 0.20mm
CONTACTS: PHOSPHOR BRONZE, THICKNESS 0.20mm
PLATING: 30μ" MIN. GOLD ON MATING AREA,
150μ" MIN. MATE TIN ON SOLDER TAILS.
ALL OVER 50μ" MIN NICKEL.
PACKAGING: TRAY PACKAGING.
TEMPERATURE RANGE: -40°C TO +85°C
STORAGE TEMPERATURE: -55°C TO +105°C

TITLE QSFP28 2X3 CAGE+CONNECTOR			深圳磁联达电子有限公司 CND-tek Shen zhen cnd-tek Electronics Co., Ltd		
PART NO. QSFP28 1717223001 2X3YDO-CND			GENERAL TOLERANCE		UNIT:MM
APPROVE	CHECK	DRAW	.X±0.20	.X±1°	SCALE: 1:1
QG.CHEN	SL.WANG	X.YAN	.XX±0.15	.XX±5°	SHEET:1/4
			.XXX±0.10		REV:A



SECTION U-U

TITLE QSFP28 2X3 CAGE+CONNECTOR			深圳磁联达电子有限公司 CND-tek Shen zhen cnd-tek Electronics Co., Ltd				
PART NO. QSFP28 1717223001 2X3YDO-CND			GENERAL TOLERANCE			UNIT:MM	SIZE: A4
APPROVE	CHECK	DRAW	.X±0.20	.X±1°	SCALE: 1:1	SHEET:2/4	REV:A
QG.CHEN	SL.WANG	X.YAN	.XX±0.15	.XX±5°			
			.XXX±0.10				




TITLE
QSFP28 2X3 CAGE+CONNECTOR

PART NO.
QSFP28 1717223001 2X3YDO-CND

APPROVE	CHECK	DRAW
QG.CHEN	SL.WANG	X.YAN

深圳磁联达电子有限公司
CND-tek Shen zhen cnd-tek Electronics Co., Ltd

GENERAL TOLERANCE	UNIT:MM	SIZE: A4
.X±0.20 .XX±0.15 .XXX±0.10	SCALE: 1:1 SHEET: 3/4	REV: A



TITLE QSFP28 2X3 CAGE+CONNECTOR			深圳磁联达电子有限公司 CND-tek Shen zhen cnd-tek Electronics Co., Ltd		
PART NO. QSFP28 1717223001 2X3YDO-CND			GENERAL TOLERANCE		UNIT:MM
APPROVE	CHECK	DRAW	.X±0.20	.X±1°	SIZE: A4
QG.CHEN	SL.WANG	X.YAN	.XX±0.15	.XX±5°	SCALE: 1:1
			.XXX±0.10		SHEET:4/4
					REV:A