









RECOMMENDED PCB LAYOUT – COMPONENT SIDE
RECOMMENDED PCB THICKNESS : 2.36MM(.093 INCH)
(MINIMUM PCB THICKNESS : 1.57)


THE ENTIRE AREA OF THE CONNECTOR FOOTPRINT
TO BE CONSIDERED THE KEEP OUT AREA FOR COMPONENTS
THIS AREA IS INDICATED BY THE DASHED LINE

TITLE SFP 2X6 CAGE+CONNECTOR			深圳磁联达电子有限公司 CND-tek Shen zhen cnd-tek Electronics Co., Ltd				
PART NO. SFP UE86-K6127-10321 2X6YD-CND			GENERAL TOLERANCE			UNIT:MM	SIZE: A4
APPROVE	CHECK	DRAW	.X±0.20	.X±1*	SCALE: 1:1	SHEET:2/4	REV:A
QG.CHEN	SL.WANG	X.YAN	.XX±0.15	.XX±5*			
			.XXX+0.10				




DETAIL-KEEPOUT ZONES

THE HATCHED AREA IN THIS VIEW INDICATES ZONES THAT ARE OCCUPIED BY THE PLASTIC HOUSING THAT SEATS AGAINST THE PCB AND BY THE VERTICAL METAL CAGE WALL THAT STOPS JUST SHORT OF THE PCB



TERMINAL TAIL PATTERN

TITLE SFP 2X6 CAGE+CONNECTOR			深圳磁联达电子有限公司 CND-tek Shen zhen cnd-tek Electronics Co., Ltd			
PART NO. SFP UE86-K6127-10321 2X6YD-CND			GENERAL TOLERANCE		UNIT:MM	SIZE: A4
APPROVE	CHECK	DRAW	.X±0.20	.X±1°	SCALE: 1:1	SHEET:3/4
QG.CHEN	SL.WANG	X.YAN	.XX±0.15	.XX±5°		
			.XXX±0.10			REV:A



BEZEL CUT-OUT CENTER SPACING DETAIL

TITLE SFP 2X6 CAGE+CONNECTOR			深圳磁联达电子有限公司 CND-tek Shen zhen cnd-tek Electronics Co., Ltd				
PART NO. SFP UE86-K6127-10321 2X6YD-CND			GENERAL TOLERANCE			UNIT:MM	SIZE: A4
APPROVE	CHECK	DRAW	.X±0.20	.X±1°	SCALE: 1:1	SHEET:4/4	REV:A
QG.CHEN	SL.WANG	X.YAN	.XX±0.15	.XX±5°			
			.XXX±0.10				