

修 订	标 记	修 改 描 要	签 名	日 期
REV	NO	REVISION DESCRIPTION	SIGNATURE	DATE
		NEW DWG		2016-03-12





NOTES:

- 1.HUOSING: LCP HIGH-TEMP THERMOPLASTIC UL94V-0 COLOR:NATURE
- 2.ACTUATOR: LCP HIGH-TEMP THERMOPLASTIC UL94V-0 COLOR:BLACK
- 3.TERMINAL:PHOSPHOR BRONZE
PLATING:1*''GOLD FLASH OR 100~150*''TIN(LEAD FREE)
OVERALL 50~100*''NICKEL UNDER PLATED.
- 4.FITTING NAIL:PHOSPHOR BRONZE
PLATING:100~150*''TIN(LEAD FREE)
OVERALL 50~100*''NICKEL UNDER PLATED.
- 5.SPECIFICATION:
CURRENT RATING: 0.5A 50V AC/DC
CONTACT RESISTANCE: 30mΩ MAX
INSULATION RESISTANCE: 100MΩ AT 500V DC
OPERATING TEMPERATURE RANGE: -40°C~85°C
WITHSTANDING VOLTANG: 500V AC/minute




NO.of contacts	Dimensions				NO.of contacts	Dimensions			
	A.	B.	C.	D.		A.	B.	C.	D.
40	27.00	19.50	24.10	27.50	69	41.50	34.00	38.60	42.00
41	27.50	20.00	24.60	28.00	70	42.00	34.50	39.10	42.50
42	28.00	20.50	25.10	28.50	71	42.50	35.00	39.60	43.00
43	28.50	21.00	25.60	29.00	72	43.00	35.50	40.10	43.50
44	29.00	21.50	26.10	29.50	73	43.50	36.00	40.60	44.00
45	29.50	22.00	26.60	30.00	74	44.00	36.50	41.10	44.50
46	30.00	22.50	27.10	30.50	75	44.50	37.00	41.60	45.00
47	30.50	23.00	27.60	31.00	76	45.00	37.50	42.10	45.50
48	31.00	23.50	28.10	31.50	77	45.50	38.00	42.60	46.00
49	31.50	24.00	28.60	32.00	78	46.00	38.50	43.10	46.50
50	32.00	24.50	29.10	32.50	79	46.50	39.00	43.60	47.00
51	32.50	25.00	29.60	33.00	80	47.00	39.50	44.10	47.50
52	33.00	25.50	30.10	33.50	81	47.50	40.00	44.60	48.00
53	33.50	26.00	30.60	34.00	82	48.00	40.50	45.10	48.50
54	34.00	26.50	31.10	34.50	83	48.50	41.00	45.60	49.00
55	34.50	27.00	31.60	35.00	84	49.00	41.50	46.10	49.50
56	35.00	27.50	32.10	35.50	85	49.50	42.00	46.60	50.00
57	35.50	28.00	32.60	36.00	86	50.00	42.50	47.10	50.50
58	36.00	28.50	33.10	36.50	87	50.50	43.00	47.60	51.00
59	36.50	29.00	33.60	37.00	88	51.00	43.50	48.10	51.50
60	37.00	29.50	34.10	37.50	89	51.50	44.00	48.60	52.00
61	37.50	30.00	34.60	38.00	90	52.00	44.50	49.10	52.50
62	38.00	30.50	35.10	38.50	91	52.50	45.00	49.60	53.00
63	38.50	31.00	35.60	39.00	92	53.00	45.50	50.10	53.50
64	39.00	31.50	36.10	39.50	93	53.50	46.00	50.60	54.00
65	39.50	32.00	36.60	40.00	94	54.00	46.50	51.10	54.50
66	40.00	32.50	37.10	40.50	95	54.50	47.00	51.60	55.00
67	40.50	33.00	37.60	41.00	96	55.00	47.50	52.10	55.50
68	41.00	33.50	38.10	41.50	97	55.50	48.00	52.60	56.00


深圳市华德共创科技有限公司
 Shenzhen Huade co-create Technology Co.,LTD
 电话：0755-27111216 传真：0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表			 		TITLE: 产品名称: FPC0.5间距2.2高掀盖式下接宽版带扣			
X.X	±0.30	X.X°	±3°	APPD: 核准:	PART NO: 产品编号: HDGC0528B~xxCL~GF			
X.XX	±0.20	X.XX°	±2°	CHECK: 校对: 王建业	DATE	SCALE	UNIT	CODE NUMBER
X.XXX	±0.10	X.XXX°	±1°	DRAW: 绘图: 黄艳兰	2016-03-12	1:1	mm	A001



CABLE INSERT DIM.
SCALE 2:1



RECOMMENDED PCB PATTERN DIM.
TOLERANCE : ±0.05

A

B

C


D

E

F


修 订	标 记	修 改 描 述	签 名	日 期
REV NO	MARK	REVISION DESCRIPTION	SIGNATURE	DATE
		NEW DWG		2016-03-12

一体膜示意图



APPLICABLE FPC/FFC

贴铝箔示意图



APPLICABLE FPC/FFC


NO.of contacts	Dimensions		NO.of contacts	Dimensions	
	B.	E.		B.	E.
40	19.50	24.05	69	34.00	38.55
41	20.00	24.55	70	34.50	39.05
42	20.50	25.05	71	35.00	39.55
43	21.00	25.55	72	35.50	40.05
44	21.50	26.05	73	36.00	40.55
45	22.00	26.55	74	36.50	41.05
46	22.50	27.05	75	37.00	41.55
47	23.00	27.55	76	37.50	42.05
48	23.50	28.05	77	38.00	42.55
49	24.00	28.55	78	38.50	43.05
50	24.50	29.05	79	39.00	43.55
51	25.00	29.55	80	39.50	44.05
52	25.50	30.05	81	40.00	44.55
53	26.00	30.55	82	40.50	45.05
54	26.50	31.05	83	41.00	45.55
55	27.00	31.55	84	41.50	46.05
56	27.50	32.05	85	42.00	46.55
57	28.00	32.55	86	42.50	47.05
58	28.50	33.05	87	43.00	47.55
59	29.00	33.55	88	43.50	48.05
60	29.50	34.05	89	44.00	48.55
61	30.00	34.55	90	44.50	49.05
62	30.50	35.05	91	45.00	49.55
63	31.00	35.55	92	45.50	50.05
64	31.50	36.05	93	46.00	50.55
65	32.00	36.55	94	46.50	51.05
66	32.50	37.05	95	47.00	51.55
67	33.00	37.55	96	47.50	52.05
68	33.50	38.05	97	48.00	52.55



深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co., LTD

电话：0755-27111216 传真：0755-29940187

-TOLERANCES-
UNLESS OTHERWISE SPECIFIED
公差参数表TITLE:
产品名称: FPC0.5间距2.2高掀盖式下接宽版带扣

X.X ±0.30 X.X* ±3°

APPD:
核准:PART NO:
产品编号: HDGC0528B-xxCL-GF

X.XX ±0.20 X.XX* ±2°

CHECK:
校对:

DATE SCALE UNIT CODE NUMBER

X.XXX ±0.10 X.XXX* ±1°

DRAW:
绘图:

2016-03-12 1:1 mm A001

A

B







C

D

E

F

修订	标记	修改摘要	签名	日期
REV	MARK	REVISION DESCRIPTION	SIGNATURE	DATE
AO		NEW DWG		2016-03-12



NOTES:

- 1.Component load per 13" reel:1500 pcs
- 2.Material: white conductive polystyrene alloy.
- 3.Thickness:0.4±0.05mm
- 4.All dimensions meet EIA-481-C requirements

No.of Contacts	DIM			REEL (CARTON)	SUM(PCS)
	A	B	C		
40pin~52pin	44	20.2	40.4	6	9000
53pin~76pin	44	52.4	26.2	5	7500
77pin~96pin	72	68.4	34.2	4	6000



深圳市华德共创科技有限公司
Shenzhen Huade co-create Technology Co.,LTD
电话：0755-27111216 传真：0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表			TITLE: 产品名称: FPC0.5间距2.2高掀盖式下接宽版带扣			
X.X	±0.30	X.X*	±3°	APPD: 核准:	PART NO: 产品编号:	HDGC0528B~xxCL~GF
X.XX	±0.20	X.XX*	±2°	CHECK: 校对: 王建业	DATE	SCALE
X.XXX	±0.10	X.XXX*	±1°	DRAW: 绘图: 黄艳兰	2016-03-12	UNIT
					1:1	CODE NUMBER
					mm	A001