




修 订	标 记	修 改 描 要	签 名	日 期
REV NO	MARK	REVISION DESCRIPTION	SIGNATURE	DATE
		NEW DWG		2016-03-12

NOTES:

- 1.HUOSING: LCP HIGH-TEMP THERMOPLASTIC UL94V-0 COLOR:BLACK
- 2.TERMINAL:PHOSPHOR BRONZE
PLATING:50u" MIN NICKEL ALL OVER 100u"MIN Tin ON SOLDER AREA
1u"GOLD FLASH ON CONTACT AREA
- 3.SHELL:STAINLESS STEEL
PLATING:100~150u" TIN(LEAD FREE)
OVERALL 50~100u" NICKEL UNDER PLATED.

4.SPECIFICATION:

CURRENT RATING: 0.5A 50V AC/DC
CONTACT RESISTANCE: 40mΩ MAX
INSULATION RESISTANCE: 100MΩ AT 500V DC
OPERATING TEMPERATURE RANGE: -55°C~+85°C
WITHSTANDING VOLTANG: 250V AC/minute







RECOMMEND P.C.B LAYOUT



深圳市华德共创科技有限公司
Shenzhen Huade co-create Technology Co.,LTD
电话：0755-27111216 传真：0755-29940187


TOLERANCES UNLESS OTHERWISE SPECIFIED 公差参数表		TITLE: 产品名称: LVDS 0.5间距3.75高51P	
X.X ±0.30	X.X* ±3°	APPD: 核准:	PART NO: 产品编号: HDGC-LVDS-51PWB
X.XX ±0.20	X.XX* ±2°	CHECK: 校对: 王建业	DATE SCALE UNIT CODE NUMBER
X.XXX ±0.10	X.XXX* ±1°	DRAW: 绘图: 黄艳兰	2016-03-12 1:1 mm A001

修 订	标 记	修 改 描 要	签 名	日 期
REV	MARK	REVISION DESCRIPTION	SIGNATURE	DATE
AO		NEW DWG		2016-03-12



NOTES:

- 1.Component load per 13" reel:1000 pcs
- 2.Material: white conductive polystyrene alloy.
- 3.Thickness:0.4±0.05mm
- 4.All dimensions meet EIA-481-C requirements



深圳市华德共创科技有限公司
Shenzhen Huade co-create Technology Co.,LTD
电话：0755-27111216 传真：0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表		TITLE: 产品名称: LVDS 0.5间距3.75高51P	
X.X ±0.30	X.X* ±3°	APPD: 核准:	PART NO: 产品编号: HDGC-LVDS-51PWB
X.XX ±0.20	X.XX* ±2°	CHECK: 校对: 王建业	DATE
X.XXX ±0.10	X.XXX* ±1°	DRAW: 绘图: 黄艳兰	SCALE
		2016-03-12	UNIT
		1:1	CODE NUMBER
		mm	A001