






RoHS



TOTAL HEIGHT		
Code	H	L
043	4.3	3.15
050	5.0	3.85
070	7.0	5.85



Product No. : TS-096-□□-□

型号:

产品高度 (H) :

043=4.3mm

050=5.0mm

070=7.0mm

弹片

D2=SUS/1PCS

D4=SUS/2PCS

操作力度:

180=180gf±50gf

250=250gf±50gf

⑤	Terminal		2	Brass	Silvering
④	Contact		1	SUS	Silver covered
③	Base		1	PPA	White
②	Cover		1	Brass	Plating Cu Sn
①	Knob		1	PPA	Black
NO.	Name	Number	Qty	Materil	Remarks

ZHONGDI®

Zhongdi Electronic Technology Co., Ltd

design	date	name	TACT SWITCHS
Review	date	model	TS-096-□□-D□
Approved	date		

Drawing number:

Proportion 1:1 unit mm gage number A4

modify Review Approved

Tolerance not specified

项 目 Item	技术参数 Technical Parameter	标 准 Standard
电气性能 Electrical Properties	额定电流 Rated Current:	50mA
	额定电压 Rated voltage:	DC 12V
	接触电阻 Contact resistance:	≤100mΩ
	绝缘电阻 Insulation Resistance:	DC 250V 1 min ≥100MΩ
	耐压强度 Compressive strength:	AC 250V 50Hz/1 min
机械性能 Mechanical Properties	机械寿命 Mechanical life:	30,000 cycles Min
	操作行程 Operation Stroke:	0.25±0.10mm
环境性能 Environmental	工作温度 Operation temperature:	-25℃~ +75℃
	使用湿度 Use humidity:	≤85% RH
可靠性特性 Reliability Characteristics	回流焊 Reflow Soldering:	
	波峰焊 Wave soldering:	≤260℃ 时间 Time 3s
	手工焊 Manual welding:	≥260℃ 时间 Time 3s
应用领域 Application area	影音产品、电子玩具、数码产品、通讯产品、安防产品等. Audiovisual products, electronic toys, digital products, communication products, security products, etc	



绝缘电阻测量仪




直流低电阻测试仪




耐电压测试仪



回流焊机



二次元测量仪



高精密寿命测试仪



盐雾测试仪



按键荷重曲线仪

ZHONGDI® 众迪 Zhongdi Electronic Technology Co., Ltd					
design		date		name	TACT SWITCHS
Review		date			
Approved		date		model	TS-096-□□-D□
number:					

modify Review Approved Tolerance not specified Proportion 1:1 unit mm gape number A4