





RoHS



Circuit Diagram



Product No. : TS-094TS-□ □ □

型号:—

—:包装方式

-P=编带(非编带,不启用)

└:弹片
D2=SUS/1PCS

操作力度：

$$120=120\text{gf} \pm 50\text{gf}$$
$$180 = 180 \text{ gf} \pm 50 \text{ gf}$$
$$250 = 250gf \pm 50gf$$

⑤	Terminal		4	Brass	Silvering
④	Reed		1	SUS	Silver covered
③	Base		1	PPA	Black
②	Cover		1	Brass	Plating Cu Sn
①	Button		1	PPA	Black
NO.	Name	Number	Qty	Materil	Remarks

ZHONGDI®
— 众迪 —

Zhongdi Electronic Technology Co., Ltd

design	
Review	
Approved	

date		name
date		

TACT SWITCHS

Approved

made

TC 004TC ☐ D ☐

modify

Review

Approved

Tolerance not specific	
------------------------	--

d Proportio

n	1:1
---	-----

	un
--	----

mit	n
-----	---

mm

gap: no

Number	
--------	--

--	--

	A
--	---

4	
---	---

项 目 Item	技术参数 Technical Parameter	标 准 Standard
电气性能 Electrical Properties	额定电流 Rated Current:	50mA
	额定电压 Rated voltage:	DC 12V
	接触电阻 Contact resistance:	≤100mΩ
	绝缘电阻 Insulation Resistance:	DC 250V 1 min ≥100MΩ
	耐压强度 Compressive strength:	AC 250V 50Hz/1 min
机械 性能 Mechanical Properties	机械寿命 Mechanical life:	500,000 cycles Min
	操作行程 Operation Stroke:	0.35±0.10mm
环境性能 Environmental	工作温度 Operation temperature:	-25℃~ +75℃
	使用湿度 Use humidity:	≤85% RH
可靠性特性 Reliability Characteristics	回流焊 Reflow Soldering:	≤260℃ 时间 Time 3s
	波峰焊 Wave soldering:	
	手工焊 Manual welding:	≥260℃ 时间 Time 3s
应用领域 Application area	影音产品、电子玩具、数码产品、通讯产品、安防产品等. Audiovisual products, electronic toys, digital products, communication products, security products, etc	



绝缘电阻测量仪




直流低电阻测试仪




耐电压测试仪



回流焊机



二次元测量仪



高精密寿命测试仪



盐雾测试仪



按键荷重曲线仪

ZHONGDI® 众迪 Zhongdi Electronic Technology Co., Ltd					
design		date		name	TACT SWITCHS
Review		date			
Approved		date			
umber:				model	TS-094TS-□D□

modify	Review	Approved	Tolerance not specified	Proportion	1:1	unit	mm	gape number	A4
--------	--------	----------	-------------------------	------------	-----	------	----	-------------	----