





RoHS



Circuit Diagram





Product No. : TS-094TS-□□□□

型号:

□: 包装方式
-P=编带(非编带, 不启用)

操作力度:
120=120gf±50gf
180=180gf±50gf
250=250gf±50gf

□: 按钮颜色
-Y=黄色
□: 弹片
D2=SUS/1PCS



PCB Layout(Pattern side)

(E)	Terminal		4	Brass	Silvering
(D)	Reed		1	SUS	Silver covered
(C)	Base		1	PPA	Black
(B)	Cover		1	Brass	Plating Cu Sn
(A)	Button		1	PPA	Yellow

ZHONGDI® — 众迪 — Zhongdi Electronic Technology Co., Ltd									
design		date		name		TACT SWITCHS			
Review		date		model		TS-094TS-□□□-Y			
Approved		date							
number:									
or	1:1	unit	mm	gage number				A4	


项 目 Item	技术参数 Technical Parameter	标 准 Standard
电气性能 Electrical Properties	额定电流 Rated Current:	50mA
	额定电压 Rated voltage:	DC 12V
	接触电阻 Contact resistance:	≤100mΩ
	绝缘电阻 Insulation Resistance:	DC 250V 1 min ≥100MΩ
	耐压强度 Compressive strength:	AC 250V 50Hz/1 min
机械 性能 Mechanical Properties	机械寿命 Mechanical life:	500,000 cycles Min
	操作行程 Operation Stroke:	0.35±0.10mm
环境性能 Environmental	工作温度 Operation temperature:	-25℃~ +75℃
	使用湿度 Use humidity:	≤85% RH
可靠性特性 Reliability Characteristics	回流焊 Reflow Soldering:	≤260℃ 时间 Time 3s
	波峰焊 Wave soldering:	
	手工焊 Manual welding:	≥260℃ 时间 Time 3s
应用领域 Application area	影音产品、电子玩具、数码产品、通讯产品、安防产品等. Audiovisual products, electronic toys, digital products, communication products, security products, etc	



绝缘电阻测量仪




直流低电阻测试仪




耐电压测试仪



回流焊机



二次元测量仪



高精密寿命测试仪



盐雾测试仪



按键荷重曲线仪

ZHONGDI® 众迪										Zhongdi Electronic Technology Co., Ltd									
design			date			name		TACT SWITCHS											
Review			date																
Approved			date			model		TS-094TS-□D□-Y											
number:																			
1:1		unit		mm		gape number								A4					