






RoHS



Circuit diagram



PCB Layout(Pattern Side)



Product No. : TS-092S-□□□□

型号:

□: 包装方式
-P=编带 (非编带, 不启用)

操作力度:
120=120gf ± 50gf
180=180gf ± 50gf
250=250gf ± 50gf

□: 按钮颜色
-W=白色
□: 弹片
D2=SUS/1PCS
D4=SUS/2PCS

Ⓕ	Dust film		1	Polyimide tape	
Ⓔ	Terminal		2	Brass	Silvering
Ⓓ	Reed		1	SUS	Silver covered
Ⓒ	Base		1	PPA	Black
Ⓑ	Cover		1	SUS	
Ⓐ	Button		1	PPA	White

ZHONGDI® — 众迪 — Zhongdi Electronic Technology Co., Ltd					
design		date		name	TACT SWITCHS
Review		date			
Approved		date		model	TS-092S-□D□-W
number:					

Drawing number: 1:1 unit mm gage number A4

modify Review Approved

angle	±2°
10~30	±0.30
5~10	±0.20
~ 5	±0.10

Tolerance not specified

Proportion

1:1

unit

mm

gage number

A4

项 目 Item	技术参数 Technical Parameter	标 准 Standard
电气性能 Electrical Properties	额定电流 Rated Current:	50mA
	额定电压 Rated voltage:	DC 12V
	接触电阻 Contact resistance:	≤100mΩ
	绝缘电阻 Insulation Resistance:	DC 250V 1 min ≥100MΩ
	耐压强度 Compressive strength:	AC 250V 50Hz/1 min
机械 性能 Mechanical Properties	机械寿命 Mechanical life:	50,000 cycles Min
	操作行程 Operation Stroke:	0.25±0.10mm
环境性能 Environmental	工作温度 Operation temperature:	-25℃~ +75℃
	使用湿度 Use humidity:	≤85% RH
可靠性特性 Reliability Characteristics	回流焊 Reflow Soldering:	≤260℃ 时间 Time 3s
	波峰焊 Wave soldering:	
	手工焊 Manual welding:	≥260℃ 时间 Time 3s
应用领域 Application area	影音产品、电子玩具、数码产品、通讯产品、安防产品等。 Audiovisual products, electronic toys, digital products, communication products, security products, etc	



绝缘电阻测量仪



直流低电阻测试仪




耐电压测试仪



回流焊机



二次元测量仪



高精密寿命测试仪



盐雾测试仪



按键荷重曲线仪

ZHONGDI® Zhongdi Electronic Technology Co., Ltd 众迪					
design		date		name	TACT SWITCHS
Review		date			
Approved		date		model	TS-092S-□D□-W
number:					

modify	Review	Approved	Tolerance not specified	Proportion	1:1	unit	mm	gape number	A4
--------	--------	----------	-------------------------	------------	-----	------	----	-------------	----