






RoHS



PCB Layout (Pattern Side)



TOTAL HEIGHT	
Code	H
015	1.5
017	1.7



Product No. : TS-064S-□□-□□



型号: □ □ □ □

产品高度 (H) : □ □ □ □
015=1.5mm
017=1.7mm

包装方式: □ □ □ □
-P=编带 (非编带, 不启用)

弹片: □ □ □ □
D2=SUS/1PCS
D4=SUS/2PCS

操作力度: □ □ □ □
180=180gf±50gf
250=250gf±50gf



Ⓕ	Dust film		1	Polyimide tape	
Ⓖ	Terminal		2	Phosphor bronze	Silvering
Ⓓ	Reed		2	SUS	Silvering covered
Ⓒ	Base		1	LCP	White
Ⓑ	Cover		1	SUS	
Ⓐ	Button		1	LCP	Black
NO.	Name	Number	Qty	Materil	Remarks

ZHONGDI® Zhongdi Electronic Technology Co., Ltd

design	date	name	TACT SWITCHS
Review	date		
Approved	date	model	TS-064S-□□-D□

Drawing number: A4

modify Review Approved Tolerance not specified Proportion 1:1 unit mm gage number


项 目 Item	技术参数 Technical Parameter	标 准 Standard
电气性能 Electrical Properties	额定电流 Rated Current:	50mA
	额定电压 Rated voltage:	DC 12V
	接触电阻 Contact resistance:	≤100mΩ
	绝缘电阻 Insulation Resistance:	DC 250V 1 min ≥100MΩ
机械性能 Mechanical Properties	耐压强度 Compressive strength:	AC 250V 50Hz/1 min
	机械寿命 Mechanical life:	100,000 cycles Min
环境性能 Environmental	操作行程 Operation Stroke:	0.15±0.10mm
	工作温度 Operation temperature:	-25℃~ +75℃
可靠性特性 Reliability Characteristics	使用湿度 Use humidity:	≤85% RH
	回流焊 Reflow Soldering:	≤260℃ 时间 Time 3s
	波峰焊 Wave soldering:	
应用领域 Application area	手工焊 Manual welding:	≥260℃ 时间 Time 3s
	影音产品、电子玩具、数码产品、通讯产品、安防产品等. Audiovisual products, electronic toys, digital products, communication products, security products, etc	



绝缘电阻测量仪




直流低电阻测试仪




耐电压测试仪



回流焊机



二次元测量仪



高精密寿命测试仪



盐雾测试仪



按键荷重曲线仪

ZHONGDI® 众迪												Zhongdi Electronic Technology Co., Ltd											
design			date			name			TACT SWITCHS														
Review			date																				
Approved			date			name			TS-064S-□□-D□														
number:																							
1:1			unit			mm			gape number						A4								