






RoHS



Circuit Diagram

PCB Layout(Pattern side)

TOTAL HEIGHT	
Code	H
018	1.8
020	2.0
025	2.5



Product No. : TS-071SA-□□-□□

型号:

产品高度(H):
018=1.8mm
020=2.0mm
025=2.5mm

操作力度:
180=180gf±50gf
250=250gf±50gf

包装方式
-P=编带(非编带, 不启用)
弹片
D2=SUS/1PCS
D4=SUS/2PCS

Ⓕ	Dust film		1	Polyimide tape	
Ⓔ	Terminal		4	Phosphorus bronze	Silvering
Ⓓ	Reed		2	SUS	Silver Covered
Ⓒ	Button		1	LCP	Black
Ⓑ	Cover		1	SUS	Natural
Ⓐ	Base		1	LCP	Black
NO.	Name	Number	Qty	Materil	Remarks

ZHONGDI®
众迪

Zhongdi Electronic Technology Co., Ltd

design	date	name	TACT SWITCHS
Review	date	model	TS-071SA-□□-D□
Approved	date		

Drawing number: A4

modify Review Approved

Tolerance not specified

Proportion

1:1

unit

mm

gaps

number

A4

