


Features :

- T-568A/B Dual wiring
- RJ45 complies with FCC part 68 standard
- Provides termination for 22~26 AWG wire
- Jack insertion life >750 mating cycles
- Operating temperature : -40°C~+60°C

Electrical :

- Contact resistance : 20m ohm
- DC Current rating : 1.5Amps
- DC resistance : Max.0.1 ohm
- Insulation Resistance : 500m ohm
- Dielectric withstanding voltage : 1000V

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

MATERIAL	
CATEGORY	■ CAT.5E ■ CAT.6 ■ CAT.6A □ CAT.7 □ CAT.8
HOUSING	ABS UL94V-0
CONTACT	0.35mm THICKNESS PHOSPHOR BRONZE GOLD PLATED OVER NICKEL
GOLD-PLATING	□ 0.0762um/3u inch □ 0.15um/6u inch □ 0.38um/15u inch □ 0.76um/30u inch □ 1.27um/50u inch
COLOR	□ WHITE □ BLACK □ GREEN □ BLUE □ YELLOW □ RED □ ORANGE □ IVORY □ OTHER _____
TYPE OF PRODUCT	□ UNSHIELD □ SHIELD : ZINC ALLOY, NICKLE PLATED.

APPROVED:	DATE:	Ckmt 深圳市灿科盟实业有限公司			
CHECKED:	DATE:	TITLE: RJ45 CAT.6A 全屏蔽直通头 带弹			
DRAWN: LYF	DATE: 2024-05-07	PART. NO.	R-RJ45Z08P-B004		
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-RJ45-0516	REV.	A ZJDZ